



**MCR
SAFETY**

N96785 Ninja Specification Sheet

PRODUCT DESCRIPTION:

Memphis Ninja® gloves are engineered to provide the highest level of innovation. Ninja® BNF (Breathable Nitrile Foam) has exceptional abrasion resistance and unparalleled grip performance. This unique polymer achieves outstanding abrasion resistance based on ASTM and CE testing. Our BNF technology provides greater comfort and longer wear due to its excellent breathability by allowing the glove to better dissipate body heat. The N96785 features a lightweight 18-gauge Nylon/Spandex shell, full coating of red flat nitrile with a second over the knuckle coating of black BNF. The double coating on the N96785 provides greater durability and creates a waterproof barrier.

FEATURES:

- Lightweight 18-Gauge Gray Nylon/Spandex Shell
- 1st Coating is Red Full Flat Nitrile Coating
- 2nd Coating is Black BNF Over The Knuckle
- Waterproof
- Slip-on, Contoured Wrist



TECHNICAL DATA FOR: N96785

Series	Ninja
Glove Size	Large
Gauge	18 Gauge
Material	Nylon
Features	Waterproof

EN 388 : CE Score - Abrasion	4
EN 388 : CE Score - Cut	1
EN 388 : CE Score - Tear	3
EN 388 : CE Score - Puncture	1
ANSI Puncture	ANSI Puncture 2
ANSI Abrasion	ANSI Abrasion 5
ANSI Contact Heat	Level 3 (Applications less than 392 degrees F)




MCR
SAFETY

N96785

Ninja

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N96785L	Large	9.842	5.551	2.362	33.408 lb.	2.784
N96785M	Medium	9.252	5.393	2.362	30.732 lb.	2.561
N96785S	Small	9.055	5.079	2.362	28.790 lb.	2.399
N96785XL	X - Large	10.630	5.905	2.559	36.096 lb.	3.008
N96785XS	X - Small	9.00	4.95	2.36	24.624 lb.	2.052
N96785XXL	XX - Large	10.826	6.063	2.559	36.876 lb.	3.073

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved