


Silt Fence

AVAILABLE ROLL DIMENSIONS AND WEIGHT

ENGLISH		METRIC	
Dimensions	Weight	Dimensions	Weight
2' x 100'	17 lbs	.61m x 30.5m	7.7 kg
3' x 100'	22.5 lbs	.915m x 30.5m	10.2 kg



Bi-Oriented Net



PHYSICAL CHARACTERISTICS

NOTES

Polymer Type	Polypropylene	
Structure	Woven	
Color	Black	
Packaging	Rolls with Wooden Stakes	
Wooden Stakes	1'' x 1'' x 36'' or 1'' x 1'' x 42''	
# Stakes Per Roll	Typically 11, may vary upon request	
# Staples Per Roll	Minimum of 4, typically 5	

TECHNICAL CHARACTERISTICS

NOTES

	ENGLISH		METRIC		
	UNIT		UNIT		
MD Tensile Strength	lbs/ft	20	kN/m	0.3	a, c
TD Tensile Strength	lbs/ft	20	kN/m	0.3	b, c
MD Trap Tear	lbs	17	kN	0.075	a, c
TD Trap Tear	lbs	14	kN	0.062	b,c
Mullen Burst	psi	120	Kpa	827	c
Puncture	lbs	30	kN	0.438	c
UV Resistance @ 500hr	%	70 retained	%	70 retained	c
Mass Per Unit Area	oz/yd ²	1.5	g/m ²	51	c
AOS	US Sieve	14	mm	1.4	c
Permittivity	sec-1	0.15	sec-1	0.15	c
Water Flow Rate	gal/min/ft ²	20	lpm/m ²	815	c

Notes

- a Longitudinal direction
- b Transversal direction
- c All dimensions and properties are reported as typical values