



STAINLESS STEEL 1 - 5/8" X 7/8" SOLID STRUT



Features:


- · Manufactured in both type 304 and 316 stainless to meet any stringent sanitary condition
- Polished to a bright, easily maintainable finish that is modern, attractive, easy to clean, and that also enhances the surface's resistance to pitting and bacterial corrosion
- · Calbrite stainless steel strut functions in exactly the same way as any other metallic strut
- Channels provided by Calbrite are available in 12 different basic sizes which are subjected to further variation in gauge and depth

Certifications and Compliances:

- UL 5B Listed
- For installation in accordance with Article 384 of ANSI/NFPA 70, National Electrical Code (NEC)

Applications:

The Calbrite system of metal framing is based on the use of a continuous slotted channel, and a series of brackets and fittings, which can be fastened to it any point. With Calbrite channel and components, racks, supports for conduit, wiring, electrical equipment, machine frames, and a limitless variety of structures can be built rapidly, simply and economically.



14 Gauge

Industries Commonly Served:

- Food & Beverage Production
- Marine & Coastal Facilities
- · Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical
- · Pulp & Paper Mills
- · Along with other corrosive environments

Type 304 Part Number	Type 316 Part Number	Size	Height of Lip	Width of Lip	Sectional Area	Weight (lbs) per L.F.
S45810SL78	S65810SL78	1 - 5/8" x 7/8"	9/32"	3/8"	.285 sq. in	1.00

All dimensions are for informational purposes only *Tolerances +/- 5%