

Product Description Sheet

LOCTITE[®] LB 8036

Known as

LOCTITE® White High Temperature Anti-Seize

January 2015

PRODUCT DESCRIPTION

LOCTITE[®] LB 8036 is a general purpose non-metallic formulation that protects against high temperature seizing and galling of mated parts. It can also be used on various metals such as copper, brass, cast iron, steel and all alloys including stainless steel.

PRODUCT FEATURES

- Typical service temperature from –29°C to 1093°C (-20°F to 2,000°F)
- Non-Metallic
- Superior water wash-out resistance
- Superior water spray resistance
- Excellent lubricity
- Prevents galvanic corrosion

TYPICAL APPLICATIONS

- Permits easy assembly and disassembly of mated parts such as bolts, screws, studs, pipe joints, nuts, shafts, bushings, splines, chains, and cables.
- Crane assemblies, ovens, power plant turbine studs, inlet heater assemblies and coal crushers.
- Pulp and paper mills, water and waste water treatment plants.

DIRECTIONS FOR USE

- 1. Clean mating surfaces before application (Remove old compound with wire brush).
- 2. Apply a thin coating to mating surfaces, do not use thinner.
- 3. Assemble parts.
- 4. Keep container closed when not in use to avoid contamination.

PROPERTIES OF MATERIAL

	Typical Value
Chemical Type	Aluminum complex
Appearance	White paste
Specific Gravity	1.10
Unworked Penetration, ASTM D-217, mm	320
Worked after 60 strokes	322
Flash Point (TCC), ºF	>200
Weight per Gallon, lbs.	9.2

TYPICAL PERFORMANCE PROPERTIES Torque Tension

Tested on degreased 3/8x16 phosphate & oil bolts and steel nuts in a Skidmore-Wilhelm apparatus. Data reported are the k-factors calculated from torque @ 5,000 lbs and 6,000 lbs tension.

Lubricity "k" Factor	Typical Value
@ 5,000 lbs	0.164
@ 6.000 lbs	0.166

T = K x F x D

- **T** = Torque (in-lb, ft-lb, N-m)
- K = Torque coefficient or nut factor, determine experimentally.
- **F** = Clamp Load (lb, N)
- **D** = Nominal diameter of bolt (in, ft, m)

Typical Performance of Material

Water washout, ASTM D1264, % Corrosion on copper, ASTM D130-94 Oil separation, FTM 791, Method 321.3, % Corrosion Resistance, Salt Fog, ASTM B117 Typical Value 0.33 No visible change 0.94 No visible change

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

Storage

Product shall be ideally stored in a cool, dry location in unopened containers at a temperature between 8°C to 28°C (46°F to 82°F) unless otherwise labeled. Optimal storage is at the lower half of this temperature range. To prevent contamination of unused product, do not return any material to its original container. For further specific shelf life information, contact your local Technical Service Center.

Data Ranges

The data contained herein may be reported as a typical value and/or range. Values are based on actual test data and are verified on a periodic basis.

Note

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results.





Product Description Sheet

LOCTITE[®] LB 8036

Known as

LOCTITE® White High Temperature Anti-Seize

January 2015

We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada, Inc.the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

In case products are delivered by Henkel Belgium NV, Henkel

Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the

following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the

following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. 0 denotes a trademark registered in the U.S. Patent and Trademark Office.

