

## **Ultra- Drum Trays**

## **Product Data Sheet**

Item Number: 1045/1046

Item Name: Ultra- Drum Trays

Sump Capacity: 22.8 Gallons (86L) without grating/ 21.1 Gallons (80L) with grating.

Item #	Color	Misc. Features	Amount	Outside Diameter	<b>Opening Diameter</b>	Height	Weight	QTY/ Pallet
1045	Yellow	Without Grate	1 Each	32" (813mm)	27 1/8" (689mm)	8 1/8" (206mm)	19 lbs. (9kg)	14
1046	Yellow/ Black	With Grate	1 Each	32" (813mm)	27 1/8" (689mm)	8 1/8" (206mm)	26 lbs. (12 kg)	14

Description: A yellow low profile polyethylene sump for the storage of 55 and 33 Gallon drums with optional grating.

Application: Designed to collect and contain drips and overflows associated with filling of 55 and 30 gallon drums.

**Product Features:** The Ultra-Drum Trays helps you comply with EPA Container Storage Regulations for 20 gallon or smaller containers.

- Molded-in sump catches leaks, drips and spills to help you comply with regulations and keep your storage area clean and safe.
- Low-profile design is perfect for spill containment of small containers.
- Optional grating elevates containers from spilled liquid, feature 21.1 gallon containment capacity with grate in place.
- Linear Low-density Polyethylene construction resists UV rays, rust, corrosion and most chemicals for long trouble-free life of the product.
- Meets EPA Container Storage Regulation for 20 gallon or smaller containers with grating in place.
- Optional dolly available for easier transport/ mobility.

**Composition:** 100% polyethylene with UV inhibitors.

Helps you comply with: EPA Regulations for storage of 20 gallon or smaller containers.

## Additional Specifications: N/A

**Disclaimers:** <u>Flammables Notice:</u> If using this product with flammable liquids, please consider the regulations that apply to storage and handling of flammable liquids and the safety of this application, specifically flammable vapors, static discharge and heat sources.