



NOTES:

- 1. WIRE CAPACITY: #10 AWG TO #6 AWG, SOLID OR STRANDED COPPER WIRE.
- 2. ALL DIMENSIONS TO BE INCHES.  
[mm]

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BASE	BAKELITE	BLACK
RETAINER	BAKELITE	BLACK
SLIDER	BAKELITE	BLACK
CONTACT SPRING	.031 BRONZE	
EYELET	.008 BRASS	
PRESSURE SCREW	STEEL	ZINC PL.
TERMINAL	COPPER	
BRIDGE	.062 STEEL	
RIVET	BRASS	ZINC PL.
AUXILIARY SPRING	.020 BRONZE	
SHUNT	.020 BRASS	
CENTER POST	STEEL	ZINC PL.
COILED SPRING	.051 MUSIC WIRE	ZINC PL.

DIMENSION SHEET FOR CAT. NO. HBL20403

REPAIRABLE  NON-REPAIRABLE

B

M-4512

2

2	ADDED NOTES 1&2; REVISED TITLE; REMOVED "SHUNT" CALLOUT; "HBL20403" WAS "20403"; REMOVED "20403-NG" CALLOUT; CONVERTED ALL DIMENSIONS TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	1/28/05
1	X REMOVED FROM CAT. NOS.		4-10-69
SYM	REVISIONS	APP	DATE

TITLE  
20A 250VDC 30A 600VAC  
4 WIRE HUBBELLOCK RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
FRACTIONS ± 1/64		BRIDGEPORT, CONN.	
DECIMALS ± .005		DR. BY A. J. L.	APP. BY
ANGLES ± 2°		TR. BY	SCALE FULL
		CHK'D. BY	DATE 8-1-66