



Available Colors: Navy, Charcoal, Brown, Red/Black, Hunter Green & Burgundy.



Estes™ features a fashionable high-low looped pile Decalon® yard that captures debris and dries foot traffic while maintaining its attractive appearance. A dense 25 ounces of tufted yarn per square yard stands up to the toughest environments, and is perfect for any main entrance way or high traffic area.


Test	Test Description	*Results
ASTM D6540	Accelerated Soiling Method	Based on Visual Inspection 5.0 - Vacuum Rating 5.0 - Rating After Extraction
ASTM D412	Breaking Load/Elongation	189.4 lbs/in ²
ASTM 5252-98a	Accelerated Wear - 4,000 cycles (Hexapod Tumble Drum Tester)	Appearance: 2.0 Color: 2.5
ASTM D3936-05	Delamination	Exceeds Backing Strength
ASTM D2240-02	Durometer (Hardness)	70
ASTM D1335-05	Tuft Bind of Pile Yarn	14.1 = Superior
CPSC FF 1-70	Surface Flammability of Carpets and Rugs Ignition Characteristics - Finished Textile Floor Covering Material	Pass

*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

07/2014

Appearance Rating Key	
5	No change
4	Slight change
3	Noticeable change
2	Considerable change
1	Severe change

- 25 oz. face weight
- Thickness: 3/8"
- Vinyl non-slip backing
- Recommended and approved product as a part of the GreenTRAX™ program for "Green Cleaning" environments
- Stock Sizes: 2' x 3', 3' x 4', 3' x 5', 3' x 6', 3' x 10', 4' x 6', 4' x 8'
- Roll Sizes: 3' x 60', 4' x 60', 6' x 60'
- Custom Sizes: In 3', 4', and 6' widths (up to 60')



Custom Sizes