

# Electric Utility Heater

HVAC/R fact sheet



## Electric Utility Heater, 5/4.1 kW

Ideal for Auxiliary, supplementary or primary heat source in factories, stores, garages, basements, warehouses, public buildings, service stations, stockrooms, offices, workshops, toll booths, closing offices, large or exposed areas or additions. Heater comes equipped with ceiling mounting bracket for horizontal or vertical flow mounting or any position in between.

CATALOG NUMBER	VOLTS	WATTS	BTU PER HR.	PHASE	HP or FAN MOTOR WATTS	FAN MOTOR RPM	AIR VOLUME CFM	THROW	MIN. MTG. HT.	HEATER AMPS	WT. (LBS.)
<b>Electric Utility Heater</b>											
3UG73	208	1874	6396	1	6	1350	270	16'	6'	9.0	24
		2500	8553							12.0	
		3123	10659							15.0	
		3750	12799							18.0	
	240	2500	8533							10.4	
		3332	11365							13.9	
		4165	14215							17.4	
		5000	17065							20.9	



## Electric Utility Heater, 5/4.1/3.3/2.5 kW

Ideal for Auxiliary, supplementary or primary heat source in factories, stores, garages, basements, warehouses, public buildings, service stations, stockrooms, offices, workshops, toll booths, closing offices, large or exposed areas or additions. Heater comes equipped with ceiling mounting bracket for horizontal or vertical flow mounting or any position in between.

CATALOG NUMBER	VOLTS	WATTS	BTU PER HR.	PHASE	HP or FAN MOTOR WATTS	FAN MOTOR RPM	AIR VOLUME CFM	THROW	MIN. MTG. HT.	HEATER AMPS	WT. (LBS.)
<b>Electric Utility Heater</b>											
3UG74	208	2500	8533	1	6	1350	270	16'	6'	10.4	24
		3332	11365							13.9	
		4165	14215							17.4	
		5000	17065							20.9	



**Exclusively from Grainger.**

Call or visit your local branch or go to [grainger.com/dayton](http://grainger.com/dayton) for complete product line information