

NO-HASSI

permanent mount only

WARRANTY

BEACONS

excluding ex R R

ECCO


> ECCO #000EL 7160 C (12 to 24 VDC 19 - 180351 5800 ET

ECCO

ECCO 7160 7160 (12 to 24 VDC (12 to 24 VDC

7160 Reflex® SAE Class I LED

The 7160 Series Reflex® LED beacon provides the ultimate level of power, versatility and style available in an LED beacon. The latest high intensity LEDs combined with reflector technology produce a powerful, SAE Class I/Cal Title 13, warning signal in a light that also offers premium features including 23 flash patterns, hi/lo intensity control and synchronization capability. Low amp draw, zero maintenance make this light an obvious choice to replace strobe or rotating lights.



Features and Benefits

- 12-24 VDC, 2.0 Amps
- High intensity LEDs and reflector technology produce an SAE Class I warning signal
- 23 flash patterns and hi/lo intensity control

ECCOESG.com

T 800-635-5900 | orders@eccogroup.com

- Multiple units can be synchronized
- Cigarette plug with on/off and flash pattern switch (vacuum magnet only)
- Temperature Range: -22°F to +122°F (-30°C to +50°C)

3.9 [99]

Flash Patterns (23)

- Steady Burn
- Title 13 Single (A)
- Title 13 Single (B)
- Title 13 Double (A)
- Title 13 Double (B)
- Title 13 Quad (A)
- Title 13 Quad (B)
- Double (A)
- Double (B)
- Fast Double (A)
- Fast Double (B)

- Quad (A)
- Quad (B)
- Quint Hold (A)
- Quint Hold (B)
- Burst (A)
- Burst (B)
- Slow Rotate
- Fast Rotate
- Wave Rotate
- Rotate/Quad
- Ramp Up/Down
- Random