



ULTRATECH
INTERNATIONAL, INC.

Ultra-Containment Berm Economy Model®

SPECIFICATIONS

KEY FEATURES AND BENEFITS

- + No frames, components or excess material outside of sidewalls — excellent for use as spill containment area inside of storage sheds and other buildings or structures where floor space is a premium.
- + Economical spill containment for frac tanks and other large containers.
- + Meets SPCC and EPA Container Storage Regulation 40 CFR 264.175.
- + Standard material of construction is Copolymer 2000™.

SIDEWALLS

- + L-shaped aluminum brackets provide sturdy sidewall support
- + Easy assembly — Brackets are quickly and easily inserted into sleeves spaced around perimeter of Containment Berm
- + Sidewalls must be put up or taken down manually when driving vehicle or equipment into Berm.

COMPLIANCE

- + EPA 40 CFR 264.175 Containment of Containers Containing Free Liquid.
- + SPCC - Spill Prevention, Control and Countermeasure Act



Part#	Dimensions ft. (m) Wall Height: 12 in. (305 mm)	Containment Capacity gal. (L)	Weight lbs. (kg)
8250	4 x 6 (1.2 x 1.8)	179 (678)	21.0 (9.5)
8251	6 x 6 (1.8 x 1.8)	269 (1,018)	26.0 (12.0)
8252	10 x 10 (3.0 x 3.0)	748 (2,831)	52.0 (23.5)
8253	12 x 60 (3.7 x 18.3)	5,385 (29,382)	268.0 (121.5)
8254	15 x 50 (4.6 x 15.2)	5,610 (21,234)	259.0 (117.5)
8255	15 x 66 (4.6 x 20.1)	7,405 (28,028)	334.0 (151.5)



PROCEDURE FOR BERM DEPLOYMENT:

STEP1: Select a level area and be sure that ground is swept clean of debris and sharp objects. The use of a ground cloth is recommended to prevent puncturing from underneath the Berm.

STEP2: Place the folded Berm at the setup location. Do not drag the folded berm. Unfold Berm and position as desired. Slide L-brackets into the Berm pockets.

STEP3: If tread protectors are being used, place these in the unit at this time.

Your Berm is now ready for use.

Storage:

1. Sweep out Berm and be sure that it is dry and free of contaminants.
2. Store unit in clean, dry environment.

Repair and Maintenance: If a puncture or tear occurs, call for a Ratching Kit. Describe the damage to the service representative to ensure receipt of the proper kit.

COPOLYMER-2000 MATERIAL SPECS

Reinforced	English	Metric	Testing Method
Base Fabric Type	Polyester		
Base Fabric Weight (nominal)	3.0 oz/yd ²	102 g/m ²	
Finished Coated Weight	28.0 ± 2 oz/yd ²	950 ± 70 g/m ²	ASTM D751
Thickness	30 mils nominal	0.76 mm nominal	ASTM D751
Trapezoid Tear	30/30 lbf nominal	133/133 N nominal	ASTM D4533
Grab Tensile	250/200 lbf min.	1112/890 N min.	ASTM D751 Grab Method
Hydrostatic Resistance	300 psi min.	2.06 MPa min.	ASTM D751, Procedure A
Adhesion	10 lbf/in min.	9.0 daN/5 cm min.	ASTM D751 Dielectric Seam
Cold Crack	Pass @ -25° F	Pass @ -32° C	ASTM D2136 1/8 in mandrel, 4 hr.
Puncture Resistance	50 lbf typical	225 N typical	ASTM D4833
Dead Load	2 in seam, 4 hr, 1 in strip 100 lbf @ 70° F 50 lbf @ 160° F	5 cm seam, 4 hr, 2.5 cm strip 445 N @ 21° C 220 N @ 70° C	ASTM D751