

SECURE JOBSITE STORAGE



DATA*VAULT*TM

DIGITALLY REACH ANY JOB, ANYWHERE



INTRODUCING

THE NEW COMPACT **118-M** DATAVAULT MOBILE






DATA VAULT™

PROBLEM

THE "LAST MILE" OF DIGITAL COMMUNICATION TO THE JOBSITE




DISTANCE=TIME=MONEY

- Unproductive "boot time" communication
- Delayed communication of latest updates
- Relies on printed files and blueprints
- Field office is not mobile or digitally connected

SOLUTION

KNAACK DATAVAULT FAMILY OF PRODUCTS DIGITALLY CONNECT ANY JOBSITE

CONNECTIVITY & PRODUCTIVITY



- Connect the Jobsite to digital assets
- Increase overall productivity
- Rugged & Secure Digital Communication
- Digitally reach any job, anywhere

MOBILITY



RUGGED SECURITY




DIGITALLY REACH ANY JOB, ANYWHERE

118-01

KNAACK DATAVAULT


• General contractor collaboration kiosk



118-M

KNAACK DATAVAULT MOBILE

• Sub/trade contractor mobile and rugged personal kiosk



**JOBSITE ACCESS TO
DIGITAL ASSETS MAXIMIZES**

- CONNECTIVITY
- PRODUCTIVITY
- MOBILITY
- RUGGED SECURITY



DATA VAULT™

CRANE LIFT KIT



40" MONITOR

View plans and specifications with a protective acrylic surface TV that is adjustable in/out



3-POSITION HATCH

independent locking hatch and pull out drawer



PRINTER

Color laser printer with AirPrint for wireless printing capabilities.



FITS THROUGH DOOR

Fits through a standard 36" wide steel frame door.



SPECIFICATIONS

UNIT WEIGHT: 780 lbs.
(fully loaded with electronics)

DIMENSIONS AS SHIPPED:
55" wide x 75" tall x 30" deep

**DIMENSIONS AFTER LIFT
BRACKETS INSTALLED:**
60.54" wide x 77" tall x 30" deep

STEEL THICKNESS:
16 gauge (14 gauge floor)

CUBIC FT. STORAGE:
Lower section: 23.35 cu. Ft.
Middle section: 5.18 cu. Ft.
Upper section: 28.99 cu. Ft.
Total=57.518 cubic ft.

118-01

KNAACK DATAVAULT

DataVault enables rugged and secure connectivity directly to the worksite, empowering productivity and digital collaboration. DataVault's customized interior arrives on the job ready for use, and is supported with a nationwide manufacture certified support network to bring agile solutions to customers.



USB SWITCH & HUB

Connect, switch, & charge mobile devices with 4port USB hub/ 2port USB switch



CABLE PASS-THROUGH

Plug & charge your laptop, tablet, phone, camera or other digital device



POWER CREW®

In box power supply provides 4 GFCI outlets for safer in-box power



BACK-UP POWER SUPPLY

1500 watt back-up power supply

OTHER FEATURES

SURGE PROTECTOR (included)

Able to withstand generator power fluctuations

CABLE HARNESS

Wire harness installed with printer, VGA, and HDMI cables

WIRELESS CAPABLE

Punch out option for wireless router (not included) for broad-band/ wifi capabilities

ADJUSTABLE

RETRACTABLE DRAWERS



DATA VAULT™

32" MONITOR

View plans and specifications



GAS STRUT SUPPORT

Dual gas strut supports on lid for easy opening



STORAGE LOCKER

Fits 5 gallon bucket of tools




4 WAY SKID ACCESS

Forklift access from all sides



FITS THROUGH DOOR

Fits through a standard 28" wide steel frame door.



118-M

KNAACK DATAVAULT MOBILE

Knaack DataVault mobile digital plan station provides a highly mobile jobsite connectivity solution, empowering productivity and digital collaboration. DataVaults arrive on the job ready for use, and are supported with a nationwide manufacturer certified support network to bring agile solutions to customers.

SPECIFICATIONS

UNIT WEIGHT: 320 lbs.
(includes TV, power crew,
power supply and cable)

STEEL THICKNESS:
16 gauge (14 gauge floor)

DIMENSIONS:
39.3" wide x 48.25" tall x
26.79" deep

CUBIC FT. STORAGE:
16.5 cubic ft.

OTHER FEATURES

SURGE PROTECTOR (included)

Able to withstand
generator power
fluctuations

CABLE HARNESS

Wire harness
installed with
VGA and HDMI
cables

WIRELESS CAPABLE

Option for wireless
router (not included)
for broadband/ wifi
capabilities

CABLE PASS- THROUGH

Plug & charge
your laptop, tablet,
phone, camera or
other digital device

POWER CREW®

In box power
supply provides 4
GFCI outlets for
safer in-box power

BACK-UP POWER SUPPLY

At least 30 minutes
of emergency power

JUNK TRUNK

QUICK ACCESS DRAWER

Heavy Duty
independent locking
drawers for quick
access to high demand
tools and accessories



OTHER KNAACK PRODUCTS

Visit knaack.com for detailed product information or to find your local dealer.

4830-D CHEST



The industry standard in jobsite security introduces the 4830-D equipped with an independent locking drawer.

79-D CHEST



Ideal for every trade, caster-ready and includes full-width shelves for organization of tools and supplies.

89-D CHEST



Ideal for mechanical trades, it is caster-ready and includes full-width shelves for organization of tools and supplies.

MONSTER BOX SERIES



Offers maximum security, weight capacity, and organization.

STORAGEMASTER® CHESTS



The workhorses on any jobsite, ideal for every trade – mechanical, plumbing, HVAC, electrical, rough and finish carpentry.

JOBMASTER® CHESTS



Available in multiple models, are the jack-of-all tradesmen chests.

JOBMASTER® CABINETS



Incredibly secure and configurable for any need.

FIELD STATION



Serves as your jobsite office.

ROLLING WORK BENCHES



Secure storage on wheels. The heavy-duty top works great as a work surface and for mounting pipe threaders or vices.

