



# LEANSAFE™

**300lbs TYPE IA**

Load Capacity

Duty Rating



Designed to lean up against walls, corners, studs, and poles



Single latch locks the rear rail to the front rail to keep the ladder in leaning mode



Curved non-marring foot pad is designed to maximize surface contact with the ground in both standard stepladder mode & leaning mode.

**NEW**



# LEANSAFE™

Standard Stepladders shouldn't be leaned against a wall, but the new Werner LEANSAFE™ ladder is designed specifically with features to safely lean against a wall, stud, corner, or pole.



Non-Marring Rubber Bumper Pad

Dropped Rail Pivot Point

Full Aluminum Bracing

Seven-Layer Fiberglass Construction

Secure Rail Latch

Model L6206

**EDGE 360**

Different Rail Color for Safety

★★★★ **300** LOAD CAPACITY lbs.

Combined Weight of User and Materials  
Type IA Duty Rating

**FIBERGLASS**  
For working around electricity  
Non-conductive side rails

## Standard Features

- Solid rivets
- Rear horizontals every 12"
- Every step is knee braced
- Internal spreaders
- EDGE360™ bracing

## SPECIFICATIONS

Model No.	Size	Stepladder Mode		Leaning Mode	
		Max. Standing Height	Max. Reach Height	Max. Standing Height	Max. Reach Height
L6204	4'	1'-8"	8'-4"	10"	7'-3"
L6206	6'	3'-10"	10'	2'-10"	9'
L6208	8'	5'-9"	12'	4'-9"	11'
L6210	10'	7'-8"	14'	6'-8"	13'
L6212	12'	9'-7"	16'	8'-7"	15'

\*assumes a 5'-6" person with a vertical 12" reach

[www.wernerco.com/us](http://www.wernerco.com/us)

WERNER CO. CORPORATE HEADQUARTERS: 93 Werner Rd., Greenville, PA 16125-9499T