

# PROFESSIONAL 21

## SERIES



WHEN THE WINTER FORECAST BRINGS A HEAVY WORKLOAD, THE NEW PROFESSIONAL 21 IS BUILT TO HANDLE THE JOB.

This single-stage workhorse was born and built to handle heavy-duty commercial detail without breaking a sweat. From starting and clearing to maintenance and transport, the Professional 21 will easily prove to be a welcome addition to any successful commercial snow clearing fleet.



### NO SWEAT START

Effortless, keyless start sequence featuring an on/off switch guarantees a successful start in any weather conditions.

### EASY OPERATION

Handlebar positions optimize system performance and user comfort.

### STRAIGHTFORWARD CLEARING

Spring-loaded, self-adjusting scraper bar follows the contours of the ground while a thick paddle cleans to the surface.

### SIMPLE MAINTENANCE

Open engine design allows access to the carburetor, recoil and spark plug.

### EFFORTLESS LOADING

Handlebar system helps guide the machine into a truck with Smart Lift.



VISIT [ARIENS.COM](http://ARIENS.COM) FOR DETAILS



DESIGNATION	PROFESSIONAL 21 SSR	PROFESSIONAL 21 SSRC
MODEL #	938024	938025
STAGE TYPE	Single-Stage	Single-Stage
ENGINE POWER	208cc (9.5 ft/lbs)	208cc (9.5 ft/lbs)
ENGINE BRAND	Ariens AX	Ariens AX
STARTING SYSTEM	Recoil	Recoil
CLEARING WIDTH	21 in (53.3 cm)	21 in (53.3 cm)
HOUSING HEIGHT	12.1 in (30.7 cm)	12.1 in (30.7 cm)
THROWING DISTANCE	3ft - 35ft (.9 - 10.7M)	3ft - 35ft (.9 - 10.7M)
CHUTE TURNING RADIUS	210°	210°
CHUTE ROTATION	Manual	Remote
DEFLECTOR CONTROL	Manual	Manual
TIRE SIZE	7.5 in x 2 in (19.1 cm x 5.1 cm)	7.5 in x 2 in (19.1 cm x 5.1 cm)
TIRE TYPE	N/A	N/A
STEERING	Solid Unlocked	Solid Unlocked
DRIVE TYPE	Auger Propelled	Auger Propelled
SPEEDS	1 Forward	1 Forward
GEAR CASE	N/A	N/A
GEAR CASE WARRANTY	N/A	N/A
IMPELLER PROFILE	N/A	N/A
IMPELLER DIAMETER	N/A	N/A
AUGER DIAMETER	8.375 in (21.3 cm)	8.375 in (21.3 cm)
AUGER TYPE	Reinforced Rubber	Reinforced Rubber
SKID SHOES	N/A	N/A
SCRAPER BAR	Polymer Self-Adjusting	Polymer Self-Adjusting
PRODUCT WARRANTY	3yr Cons, 1 yr Comm	3yr Cons, 1 yr Comm
LENGTH	50.8 in (128.9 cm)	50.8 in (128.9 cm)
WIDTH	21.2 in (53.8 cm)	21.2 in (53.8 cm)
HEIGHT	41.7 in (105.9 cm)	41.7 in (105.9 cm)
WEIGHT	87 lb (39.46 kg)	89 lb (40.37 kg)
FEATURES AT A GLANCE	Smart Lift handlebar system, Hour Meter	Smart Lift Handlebar system, Hour Meter, Mechanical chute rotation