



POWERED BY SCHUMACHER

STRONGER THAN EVER.



DSR
POWERED BY SCHUMACHER

PROSERIES

VOLTAGE $\frac{V}{\text{V}}$

CURRENT $\frac{A}{\text{A}}$

BATTERY % $\frac{\%}{\%}$

AUTO

125A

15 <- 40A
BURST/REVERSE MODE

6 <- 2A

FULLY AUTOMATIC
MICROPROCESSOR CONTROLLED

PRESS BUTTON TO SELECT MODE,
MONITOR STATUS ON DISPLAY.

UL LISTED
HOUSEHOLD
BATTERY CHARGER
104-3

BC

READ WARNING ON BACK AND INSTRUCTION MANUAL

INPUT: INPUT: 120V AC, 5.2A MAXIMUM CONTINUOUS, 25A INTERMITTENT. SUPPLY: 6.0V DC, 30A/15A CONTINUOUS, 40A INTERMITTENT.
40 SECONDS MAXIMUM ON, 120 SECONDS MINIMUM OFF, 125A INTERMITTENT 5 SECONDS MAXIMUM ON, 180 SECONDS MINIMUM OFF

0899009662

125 ENGINE START

DSR
POWERED BY SCHUMACHER

PROSERIES

CHARGING $\frac{V}{\text{V}}$

CHARGED/MAINTAINING $\frac{\%}{\%}$

START STOP

CLAMP REVERSED

BAD BATTERY

AUTOMATICALLY SELECTS CHARGE RATE
FOR CHARGING AND MAINTAINING

SERVICE MODE - press and hold start/stop button until LED lights.

BC

10 Amp Charger



POWERED BY SCHUMACHER

PROSERIES



DSR118

6V/12V Battery Charger

125A Engine Start

15 ↔ 40A Boost/Service | 6A ↔ 2A Charge

- **125A Engine Start** - powerful enough for SUVs, trucks and large engines
- **15↔40A Boost Mode** – ramps up the voltage and sends a quick burst of energy into the battery quickly bring deeply discharged batteries back to life.
- **15↔40A Service Mode** – maintains a stable voltage at 13.6V and prevents discharged batteries during service or sitting idle in a showroom.
- **6A↔2A** - Charge keeps stored, lead-acid batteries charged; charges and maintains small batteries
- **Fully Automatic** - prevents overcharging by monitoring and switching to maintenance mode when fully charged
- **LED Indicators & Touch pad Controls** - for ease and accuracy
- **Built-in Cord Management** - unique recessed channel keeps power cord and cables neatly wrapped for storage
- **High-impact Molded Case** - rustproof and non-conductive
- **Battery Tester** - provides charge level and helps diagnose electrical problems
- **Scrolling Digital Display** - The easy-to-read, animated display gives you step by step instructions to properly charge your battery.
- **125A Clamps with copper cable** - for top- and side-mount battery posts
- **Auto Voltage Detection** - automatically detects 6V or 12V batteries
- **Reverse Hook-up Protection** - charger does not operate if clamps are reversed on the battery. LED will light

Powerful Performance.

DSR117

12V Battery Charger

10A Rapid Charge

13.6V Service Mode

- **Microprocessor Controlled** - Automatically adjusts the amperage rate to charge & maintain. Multi-stage charging for added precision, safety & battery life
- **LED Indicators** - Show charging status
- **Compatible Battery Types** - Standard, AGM & GEL
- **Reverse Hook-up Protection** - Charger will not operate if clamps are reversed
- **Hook Attachment** - Allows unit to hang safely outside the work area
- **Schu Eco Energy** - Meets the highest industry standards for energy efficiency
- **13.6V Service mode** - maintains a stable voltage at 13.6V and prevents discharged batteries during service or sitting idle in a showroom.

