



Ultra-Dewatering Bags® Specifications

Material Specifications

Properties	ASTM Test	Value
Material: Non-Woven, Polyethylene Geotextile	-	-
Grab Tensile	D 4632	205 lbs
Elongation at break	D 4632	50%
Trapezoid Tear	D 4533	80 lbs
Puncture	D 4833	525 lbs
Mullen Burst	D 3786	420 psi
Permittivity	D 4491	1.5 sec ⁻¹
A.O.S. (U.S. sieve no.)/ mm	D 4781	80/0.18
UV Stability (strength retained %) 500 Hours	D 4355	70%
Fabric Weight (oz./yd²)(typical)	D 5261	8 oz/yd ²
Flow Rate	D 4491	90 gpm/ft ²

Install the Ultra-Dewatering Bag® on a slope so incoming water flows downhill through the Ultra-Dewatering Bag® without creating more erosion. Strap the neck of the Ultra-Dewatering Bag® tightly to the discharge hose. To increase the efficiency of filtration, place the bag on an aggregate or hay bale bed to maximize water flow through the surface area of the bag.

The Ultra-Dewatering Bag® is full when it no longer can efficiently filter sediment or pass water at a reasonable rate. Flow rates will vary depending on the size of the Ultra-Dewatering Bag®, the type and amount of sediment discharged into the Ultra-Dewatering Bag®, the type of ground, rock or other substance under the bag and the degree of the slope on which the bag lies. Under most circumstances Ultra-Dewatering Bag® will accommodate flow rates of 1500 gallons per minute. Use of excessive flow rates or overfilling Ultra-Dewatering Bag® with sediment will cause ruptures of the bags or failure of the hose attachment straps.

Dispose of the Ultra-Dewatering Bag® as directed by the site engineer. If allowed, the Ultra-Dewatering Bag® may be cut open and the contents seeded after removing visible fabric.

The facts stated and the recommendations made herein are offered free of charge and are accurate to the best of our knowledge. UltraTech International, Inc. assumes no liability for the accuracy or completeness of this information or for the ultimate use by the purchaser. UltraTech disclaims any and all express, implied, or statutory standards, warranties or guarantees, including without limitation any implied warranty as to merchantability or fitness for a particular purpose or arising from a course of dealing or usage of trade as to any equipment, material, or information furnished herewith. Final determination of the use of any information or material, or how it is useful, and whether the use infringes any patents is the sole responsibility of the user.

Unit Specifications

Model	Fabric QTY	Max Flow Rate (GPM)	Sediment Capacity (Cu Ft)	Sediment Capacity (lbs.)	Oil Capacity
Oil & Sediment 3'x4' Part # 9729-0/S	24 sq ft	500	6	720	1.2 gal
Oil & Sediment 6'x6' Part # 9724-0/S	74 sq ft	500	36	4320	3.7 gal
Oil & Sediment 10'x15' Part # 9725-0/S	302 sq ft	500	150	18000	15.1 gal
Oil & Sediment 15'x15' Part # 9727-0/S	452 sq ft	500	225	27000	22.6 gal