

BILLY GOAT®



QV QUIETVAC™
Quiet, low dust cleanup with Billy Goat

Vac it With Ease: Low Dust Low Noise Superior Lift Power


This Unit Features:

- World's quietest vacuum
- Unique cyclonic filtration with exclusive Dust Sock™ technology virtually reduces dust in dry conditions
- Optional self-propelled hydro drive shift-on-the-fly transmission with infinite forward/reverse speeds
- 33" wide productivity with composite intake and cyclonic hood
- 6-blade armor plate steel fan; up to 12 to 1 reduction for composting in dry conditions
- Optional on board hose kit expands to 10' for easy reach in hard to get to places (hose kit has ergonomic handle extension and simple intake door lock)
- Unique volute housing and fan combination for optimum suction power
- Two-latch bag for hassle-free loading and unloading – 36 gal. bag capacity
- Rear turf tires and front casters for smooth fingertip maneuverability.
- Optional parking brake kit (Part #831609)



Shown with
optional hose kit

Patents Pending

 Made in the USA

Quiet, low dust cleanup with Billy Goat!

www.billygoat.com




Features and Specifications



BEST IN CLASS NOISE REDUCTION
 QV has the lowest dB in its class compared to other vacs on the market with equal engines at the same RPM.



TWO-LATCH BAG
 Unloading and loading is a cinch with the two-latch pivoting bag system.



STATE OF THE ART CYCLONIC FILTRATION
 Innovative cyclonic filtration with exclusive Dust Sock™ technology virtually reduces dust in dry conditions.



LARGE CAPACITY TURF BAG
 holds 36 gallons. Add Dust Sock™ (Part #831282) for minimal dust in dry conditions (comes standard). Optional debris bag skirt, Part #831268.



OPTIONAL COLLAPSIBLE ON BOARD HOSE KIT WITH ERGONOMIC HANDLE EXTENSION
 User-friendly on board hose kit expands to 10'. Magnetic intake door closure provides trouble-free switching to clean hard to reach areas. (Part #831018)



POWERFUL SUCTION AT VARIABLE HEIGHTS
 Readily adjust height from ½" to 3" to accommodate any surface needs. Combined with the unique volute housing and fan system, the QV offers the best suction power of any litter vacuum on the market today - at any height.



HYDRO-DRIVE TRANSMISSION MANEUVERS LIKE A DREAM
 Hydrostatic transmission with infinite forward and reverse speeds, 0-3 mph, and shift on the fly offers nimble movability. Negotiate tight spots quickly and with unbelievable ease. (QV550HSP, QV900HSP models)



DURABLE FRONT CASTERS ROLL SMOOTHLY
 through turns and over uneven surfaces offering quick task completion.

POWERED BY
HONDA

Model	Engine	Propulsion	Nozzle Width	Weight	Length	Width	Height
QV550	205 cc Briggs	Push	33"	180 lbs (81 kg)	63" (160 cm)	33" (83.8 cm)	51" (129.5 cm)
QV550H	160 cc Honda	Push	33"	175 lbs. (79.4 kg)	63" (160 cm)	33" (83.8 cm)	51" (129.5 cm)
QV550HSP	160 cc Honda	Hydro Drive	33"	226 lbs. (102.5 kg)	63" (160 cm)	33" (83.8 cm)	51" (129.5 cm)
QV900HSP	270 cc Honda	Hydro Drive	33"	248 lbs (112.5 kg)	63" (160 cm)	33" (83.8 cm)	51" (129.5 cm)

Part #831502

For more information or to find a dealer near you, visit www.billygoat.com