



**MAX PERFORMANCE
EXTREME HEAVY-DUTY
BUILT FOR STARTING**



FULLY AUTOMATIC

BATTERY CHARGER ENGINE STARTER

FOR ADVANCED DIAGNOSTIC TESTING, ENGINE STARTING & CHARGING

SC1362



ENGINE START



BATTERY TYPES:
STANDARD AGM
DEEP-CYCLE

30A
BOOST

6 <-> 2A
CHARGE / MAINTAIN



85A ENGINE STARTER

POWERFUL ENOUGH FOR STARTING SUVs AND TRUCKS.

BATTERY AND ALTERNATOR TESTER

PROVIDES CHARGE LEVEL AND HELPS DIAGNOSE ELECTRICAL PROBLEMS.

DIGITAL DISPLAY, LED INDICATORS AND BUTTON CONTROLS

FOR EASE AND ACCURACY

SCHU ECO ENERGY

MEETS THE HIGHEST INDUSTRY STANDARDS FOR ENERGY EFFICIENCY

CHARGES COMPATIBLE BATTERY TYPES

STANDARD, AGM & DEEP-CYCLE BATTERIES

MICROPROCESSOR CONTROLLED

AUTOMATICALLY ADJUSTS THE AMPERAGE RATE TO CHARGE & MAINTAIN.
MULTI-STAGE CHARGING FOR ADDED PRECISION, SAFETY & BATTERY LIFE.

FLOAT-MODE MONITORING

AUTOMATICALLY MAINTAINS OPTIMUM BATTERY CHARGE.

AUTO VOLTAGE DETECTION

AUTOMATICALLY DETECTS 6 OR 12 VOLT BATTERIES.

REVERSE HOOK-UP PROTECTION

CHARGER WILL NOT OPERATE IF CLAMPS ARE REVERSED. INDICATOR WILL FLASH.



**MAXIMIZING
ENERGY EFFICIENCY**

SUPERIOR PERFORMANCE