



Available Colors: Charcoal, Autumn Brown, Gray, Burgundy, Hunter Green.



Arrow Trax™ provides exceptional performance in highly visible areas that require a subtly attractive yet functional floor mat. The durable herringbone patterns offers non-directional scraping action and moisture retention, and a full 38 ounces of needle punched yarn per square yard provides the highest degree of crush resistance in heavy traffic areas.

Test	Test Description	*Results
ASTM 5252-98a	Accelerated Wear - 4,000 cycles (Hexapod Tumble Drum Tester)	Appearance: 2.3 Color: 3.0
ASTM D3936-05	Delamination	Exceeds backing strength
ASTM D6540-05	Accelerated Soiling	Based on Visual Inspection 5.0 - Vacuum Rating 5.0- Rating After Extraction
ASTM D412	Breaking Load/Elongation	227.2 lbs/in ²
ASTM D1894-08 (modified)	Static & Kinetic Coefficient of Friction	1.20
ASTM D2859 (CPSC FF 1-70)	Flammability	Pass

*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

07/2014

Appearance Rating Key	
5	No change
4	Slight change
3	Noticeable change
2	Considerable change
1	Severe change

- Face Weight: 38 oz. per sq. yd.
- Thickness: 3/8"
- Vinyl non-slip backing
- Recommended and approved product as a part of the GreenTRAX™ program for "Green Cleaning" environments
- Stock Sizes: 2' x 3', 3' x 4', 3' x 5', 3' x 6', 3' x 10', 4' x 6', 4' x 8'
- Roll Sizes: 3' x 60', 4' x 60', 6' x 60'
- Custom Sizes: In 3', 4', and 6' widths (up to 60')



Custom Sizes

