


[®]
WESTWARD



(EXTENSION LADDER)

**Models 44YY67, 44YY15, 44YY60,
44YY49, 44YY58, 44YY21, 44YY40,
44YY45, 44YY56, 44YY46, 44YY43,
44YY20, 44YY62, 44YY57, 44YY17**

HOW TO SELECT A LADDER

1 Select a Type



STEP LADDER

TWIN FRONT LADDER

PLATFORM LADDER

EXTENSION LADDER

The most popular style of ladder. Used from medium to low heights. Utilize pail shelves and tops to hold tools for the job.

Allows two users to work on the same ladder simultaneously. Easily accomplish tasks that would be more difficult for a single person.

Combine step ladder and warehouse ladder technology. The non-pinch platform provides a large standing area for work.

The most versatile style of ladder, found in a variety of sizes. Most commonly used for higher elevations.

2 Select a Height

STEP LADDERS

LADDER SIZE	APPROX. HIGHEST STANDING LEVEL	MAXIMUM REACH
4'	1' 11"	8' 6"
5'	2' 10"	9' 5"
6'	3' 9"	10' 4"
7'	4' 9"	11' 4"
8'	5' 8"	12' 3"
10'	7' 7"	14' 2"
12'	9' 6"	16' 1"
14'	11' 5"	18'
16'	13' 4"	19' 11"
18'	15' 3"	21' 10"
20'	17' 2"	23' 9"

EXTENSION LADDERS

LADDER SIZE	MAXIMUM EXTENDED LENGTH	MAX. REACH*	WORKING RANGE TO TOP SUPPORT*	MAXIMUM ACCESSIBLE ROOF HEIGHT RANGE*
16'	13'	16' 1"	7 ½' - 12 ½'	4 ½'-9 ½'
20'	17'	20'	9 ½' - 16 ½'	6 ½'-13 ½'
24'	21'	23' 10"	11 ½' - 20'	8 ½'-17'
28'	25'	27' 9"	13 ½' - 24'	10 ½'-21'
32'	29'	31' 7"	15 ½' - 28'	12 ½'-25'
36'	32'	34' 6"	17 ½' - 31'	14'-28'
40'	35'	37' 5"	19' - 33 ½'	16'-30 ½'
44'	39'	41' 3"	21' - 37 ½'	18'-34 ½'
48'	43'	45' 2"	23' - 41 ½'	20'-38 ½'
60' *	48'	50'	23' - 46 ½'	20'-43 ½'

*Assumes 5' 7" person with 12" vertical reach |

**When set up at the proper 75 1/2° angle | **Three-section extension ladder

HOW TO SELECT A LADDER (CONTINUED)

3 Select a Load Capacity



TYPE IAA: Professional use. Extra heavy duty. Capable of supporting 375 lbs.

USES: MRO and industrial construction.



TYPE IA: Professional use. Extra heavy duty. Capable of supporting 300 lbs.

USES: Roofing, building maintenance, contracting and industrial construction.



TYPE I: Industrial use. Heavy duty. Capable of supporting 250 lbs.

USES: Building maintenance, general contracting and sheet rock.



TYPE II: Commercial use. Medium duty. Capable of supporting 225 lbs.

USES: Light commercial and general repair, painting and cleaning.



TYPE III: Household use. Light duty. Capable of supporting 200 lbs.

USES: Light cleaning and painting.

4 Select a Ladder Material



DO NOT USE ALUMINUM LADDERS NEAR ELECTRICITY

ALUMINUM

- ▶ Lightweight
- ▶ Long-lasting construction
- ▶ Resists corrosion
- ▶ Ideal for painting, roofing and siding



FIBERGLASS LADDERS ARE SAFE FOR WORKING AROUND ELECTRICITY

FIBERGLASS

- ▶ Non-conductive when clean and dry
- ▶ Strong and durable
- ▶ Weather-resistant
- ▶ Great for heavy-duty construction

AT LOUISVILLE LADDER, all of our products are designed and constructed to meet or exceed applicable standards and requirements of the American National Standards Institute (ANSI), Occupational Safety and Health Administration (OSHA), and Canadian Standards Association (CSA). Please read the information on this page before using our products. Your safety is important to us.

ANSI

Meets or exceeds requirements of American National Standards Institute

Louisville Ladder, Inc. manufactures products in compliance with the applicable safety codes of the **AMERICAN NATIONAL STANDARDS INSTITUTE (ANSI)**. There are a variety of ANSI safety codes depending on material and type of ladder. You can find a list of them in the figure on the right. In addition, ANSI codes have established a Duty Rating which identifies the use for which a portable ladder is intended and the conditions under which the ladder can be used safely. An extensive series of tests and design requirements determines which Duty Rating label a particular ladder may receive. The total load supported includes the combined weight of the user, clothing, tools and any materials on the ladder. However, ladders must be used properly in order to support the intended load.

FIBERGLASS LADDERS: ANSI A14.5

METAL LADDERS: ANSI A14.2

HOW TO SELECT A LADDER (CONTINUED)



The **OCCUPATIONAL SAFETY & HEALTH ADMINISTRATION (OSHA)** regulates the adequacy of ladders and the work practices followed by employees using them in five sections: Portable Wood (1910.25), Portable Metal (1910.26), Fixed Ladders (1910.27), Mobile Ladder Stands and Scaffolds (1910.29) and ladders used in Construction Industry (1926.1053). These sections specify the standards to which all portable ladders must be manufactured, care and placement of ladders in the workplace, and the safe use of ladders on the job.

OSHA sets minimum national requirements with respect to the use of ladders in business and industry. However, many states have enacted their own regulations under the Occupational Safety & Health Act that establish more severe requirements. The more demanding state codes will supersede OSHA standards within their respective states. Therefore, users should check with their own state OSHA representatives.



Where applicable, product meets or exceeds **CANADIAN STANDARDS INSTITUTE** testing

LADDER INSPECTION

Look for damaged or missing parts

Always check for damage before using any ladder. Do not use a damaged ladder. Conduct your inspection before you leave for the job site.

1. Begin at the bottom, making sure the feet are not broken or malfunctioning and that the slip-resistant pads are secure.
2. Inspect the ladder for cracks, bends, and splits on side rails, rungs, and steps.
3. Check all rung/step-to-side rail connections, as well as hardware, fittings, and accessories. Make sure both rung locks are in working order.
4. Test the rope and pulley for smooth operation. Replace the rope if frayed or partially cut.
5. All pivotal connections and the rung-locks should be well-lubricated.
6. All bolts and rivets should be secure. Never use a ladder if any bolts or rivets are missing or if the joints between the steps (or rungs) and the side rails are not tight.
7. Make sure the ladder (particularly the steps and rungs) is free of foreign materials such as oil and grease.
8. If you're using a stepladder, make sure the spreader braces are not bent, are secure and working properly.

Use a ladder-inspection chart as a guide for evaluating the safety of a ladder.

Remember to inspect the ladder before you travel to the job site, because once you're there you'll be tempted to use the ladder regardless of its condition.

Always mark unsafe ladders by using a damaged-ladder tag (see sample illustration).

Be sure to store damaged ladders away from usable ladders. Have them repaired as soon as possible. Destroy unrepairable ladders immediately.

Transporting a ladder

Accidents can happen while transporting the ladder to the job site. A ladder is long and awkward, and can cause injuries and property damage during transport. When possible, two people should carry an extension ladder. If you carry it yourself, keep the front end of the ladder slightly higher than the back end.

Never move or reposition an extension ladder without completely retracting the fly section. Failure to do so can cause serious injury or death.

Secure both ends of a ladder when transporting it on a vehicle. Use care when placing ladders onto or removing from ladder racks.

DANGER

DAMAGED LADDER

DO NOT USE

INSPECTED BY: _____

DATE: __/__/__

Destroy & Dispose

Repair _____



INSTRUCTIONS- EXTENSION LADDER (CONTINUED)

Consider before each use

1. Metal ladders conduct electricity. Keep away from electrical circuits.
2. Consult manufacture for use in chemical or other corrosive environments.
3. Use a ladder only as outlined in instructions. Ladders are designed for one person only. DO not overload.
4. DO not use in high winds or during storms.
5. DO not use in poor health, if taking drugs or alcoholic beverages, or if physically handicapped.
6. Keep shoes clean. Leather soles should not be worn.
7. Never leave ladder set up and unattended.
8. Pay close attention to what you are doing.
9. Use this product at your own risk.

Proper set-up and use

1. Use help in setting up multi-purpose ladder, if possible.
2. Make sure ladder is fully open and hinges locked.
3. Set all feet on firm level surface. Do not place on unstable, loose, or slippery surfaces. Place multi-purpose ladders where access is not obstructed. Do not place in front of unlocked doors. multi-purpose ladders are not intended to be used on scaffolds.
4. Secure multi-purpose ladder from movement where possible.
5. Make sure hinges are locked and multi-purpose ladder is stable before climbing.
6. Face multi-purpose ladder when climbing up or down. Maintain a firm grip. Use both hands in climbing.
7. Keep body centered between side rails. Do not over reach. Get down and move multi-purpose ladder as needed.
8. Do not climb, stand or sit above second step from the top.
9. Do not straddle front and back. Do not climb from one multi-purpose ladder to another.
10. Avoid pushing or pulling off to side of multi-purpose ladder. Do not "walk" or "shift" the ladder while on it.
11. When using for access to roof, extend ladder top 3 feet above roof edge. Tie or secure top from movement.

Proper climbing and use

1. Making sure runglocks are engaged before climbing.
2. Face ladder when climbing up or down, maintain a firm grip. Use both hands climbing
3. Keep body centered between side rails. Do not overreach. Get down and move ladder as needed.
4. Do not stand higher than 3 feet from the top of the ladder. Do not climb above top support point. Do not climb from one ladder to another.
5. Avoid pulling or pushing off to the side of ladder. Do not "walk" or "shift" ladder while on it.
6. Never drop or apply an impact load to ladder.
7. Fly section must have safety shoes if used as a single ladder.
8. Never use ladder jacks on Type II or Type III extension ladders.




INSTRUCTIONS- EXTENSION LADDER (CONTINUED)

Proper care and storage

1. Hang ladder on racks at intervals of 6' for support.
2. Securely support ladder in transit.
3. Never store materials on ladder.
4. Always keep ladder clean of all foreign materials.

1. Do not let any ladder contact electrical wires.
2. Retract ladder sections fully before lifting or moving.
3. Raise and lower ladder from ground only; never from top.
4. Do not use on slippery surface without securing from movement.



75 DEGREE SET-UP ANGLE

- A. Place toes against bottom of ladder side rails.
- B. Stand erect.
- C. Adjust angle so you can grasp lower section rails as shown at shoulder level with arms straight.

WESTWARD ONE-YEAR LIMITED WARRANTY

WESTWARD ONE-YEAR LIMITED WARRANTY. All Westward® product models covered in this manual covered by this Limited Warranty are warranted by W.W. Grainger, Inc. ("Grainger") to the original user against defects in workmanship or materials under normal use for one year after date of purchase. If the Product is part of a set, only the portion that is defective is subject to this warranty. Any Product or part which is determined to be defective in material or workmanship and returned to an authorized service location, as Grainger or Grainger's designee designates, shipping costs prepaid, will be, as the exclusive remedy, repaired or replaced with a new or reconditioned product or part of equal utility or a full refund given, at Grainger's or Grainger's designee's option, at no charge. For limited warranty claim procedures, see "Warranty Service" below.

COVERED PRODUCTS. This Limited Warranty covers the product model(s) identified in this manual. This Limited Warranty does not cover normal wear and tear of Products or portions of them, or products or portions of them which are consumable in normal use. This warranty is void if there is evidence of misuse, mis-repair, mis-installation, abuse or alteration.

WARRANTY DISCLAIMERS AND LIMITATIONS OF LIABILITY RELATING TO ALL CUSTOMERS FOR ALL PRODUCTS

LIMITATION OF LIABILITY. TO THE EXTENT ALLOWABLE UNDER APPLICABLE LAW, GRAINGER'S LIABILITY FOR CONSEQUENTIAL AND INCIDENTAL DAMAGES IS EXPRESSLY DISCLAIMED. GRAINGER'S LIABILITY IN ALL EVENTS IS LIMITED TO AND SHALL NOT EXCEED THE PURCHASE PRICE PAID.

WARRANTY DISCLAIMER. A DILIGENT EFFORT HAS BEEN MADE TO PROVIDE PRODUCT INFORMATION AND ILLUSTRATE THE PRODUCTS IN THIS LITERATURE ACCURATELY; HOWEVER, SUCH INFORMATION AND ILLUSTRATIONS ARE FOR THE SOLE PURPOSE OF IDENTIFICATION, AND DO NOT EXPRESS OR IMPLY A WARRANTY THAT THE PRODUCTS ARE MERCHANTABILITY, OR FIT FOR A PARTICULAR PURPOSE, OR THAT THE PRODUCTS WILL NECESSARILY CONFORM TO THE ILLUSTRATIONS OR DESCRIPTIONS. EXCEPT AS PROVIDED BELOW, NO WARRANTY OR AFFIRMATION OF FACT, EXPRESSED OR IMPLIED, OTHER THAN AS STATED IN THE "LIMITED WARRANTY" ABOVE IS MADE OR AUTHORIZED BY GRAINGER.

PRODUCT SUITABILITY. MANY JURISDICTIONS HAVE CODES AND REGULATIONS GOVERNING SALES, CONSTRUCTION, INSTALLATION, AND/OR USE OF PRODUCTS FOR CERTAIN PURPOSES, WHICH MAY VARY FROM THOSE IN NEIGHBORING AREAS. WHILE ATTEMPTS ARE MADE TO ASSURE THAT PRODUCTS COMPLY WITH SUCH CODES, GRAINGER CANNOT GUARANTEE COMPLIANCE, AND CANNOT BE RESPONSIBLE FOR HOW THE PRODUCT IS INSTALLED OR USED. BEFORE PURCHASE AND USE OF A PRODUCT, REVIEW THE SAFETY/SPECIFICATIONS, AND ALL APPLICABLE NATIONAL AND LOCAL CODES AND REGULATIONS, AND BE SURE THAT THE PRODUCT, INSTALLATION, AND USE WILL COMPLY WITH THEM.

CONSUMERS ONLY. CERTAIN ASPECTS OF DISCLAIMERS ARE NOT APPLICABLE TO CONSUMER PRODUCTS SOLD TO CONSUMERS; (A) SOME JURISDICTIONS DO NOT ALLOW THE EXCLUSION OR LIMITATION OF INCIDENTAL OR CONSEQUENTIAL DAMAGES, SO THE ABOVE LIMITATION OR EXCLUSION MAY NOT APPLY TO YOU; (B) ALSO, SOME JURISDICTIONS DO NOT ALLOW A LIMITATION ON HOW LONG AN IMPLIED WARRANTY LASTS, SO THE ABOVE LIMITATION MAY NOT APPLY TO YOU; AND (C) BY LAW, DURING THE PERIOD OF THIS LIMITED WARRANTY, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE APPLICABLE TO CONSUMER PRODUCTS PURCHASED BY CONSUMERS, MAY NOT BE EXCLUDED OR OTHERWISE DISCLAIMED.

THIS LIMITED WARRANTY GIVES YOU SPECIFIC LEGAL RIGHTS, AND YOU MAY ALSO HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.

THIS LIMITED WARRANTY ONLY APPLIES TO PRODUCTS PURCHASED BY UNITED STATES PURCHASERS FOR DELIVERY IN THE UNITED STATES.

WARRANTY SERVICE

To obtain warranty service if you purchased the covered product directly from Grainger, (i) write or call or visit the local Grainger branch from which the product was purchased or another Grainger branch near you (see www.grainger.com for a listing of Grainger branches); or (ii) contact Grainger by going to www.grainger.com and clicking on the "Contact Us" link at the top of the page, then clicking on the "Email us" link; or (iii) call Customer Care (toll free) at 1-888-361-8649. To obtain warranty service if you purchased the covered product from another distributor or retailer, (i) go to www.grainger.com for Warranty Service; (ii) write or call or visit a Grainger branch near you; or (iii) call Customer Care (toll free) at 1-888-361-8649. In any case, you will need to provide, to the extent available, the purchase date, the original invoice number, the stock number, a description of the defect and anything else specified in this Westward One-Year Limited Warranty. You may be required to send the product in for inspection at your cost. You can follow up on the progress of inspections and corrections in the same ways. Title and risk of loss pass to buyer on delivery to common carrier, so if product was damaged in transit to you, file claim with carrier, not the retailer or Grainger. For warranty information for purchasers and/or delivery outside the United States, please contact:

Canada: www.westwardtools.ca

Mexico: Grainger.com.mx

Location not listed, contact: +1-888-361-8649 (or 1-800-GRAINGER)