

The logo features the letters 'DSX' in a bold, italicized, sans-serif font. A thick, grey swoosh arches over the letters, starting from the top left and ending at the top right. The letters are a light grey color against a dark grey background.

DSX

DOCKING STATION

INDUSTRIAL

SCIENTIFIC



THE DSX **DOCKING STATION**

The DSX™ Docking Station easily maintains the gas detectors that keep your people safe in hazardous environments.

YOUR GAS DETECTORS **READY WHEN YOU NEED THEM**

Know that your instruments are ready for use every day, every shift,
without the burden of manual maintenance routines.



YOUR CALIBRATION GAS
THERE BEFORE YOU RUN OUT

Stop worrying about calibration gas and let DSX monitor and order replacement gas cylinders when you need them.

YOUR SOFTWARE **UPDATED UPON RELEASE**

Effortlessly manage your fleet, data, and software updates from any web-enabled device.



Post

www.indsci.com
https://inet.indsci.com/NetCustomerUI/

12:11 PM

86%

iNetControl

Account: ISC Sales >

Home Feed Settings Reports Help

ISC Sales Demo Equipment - 131931

Welcome engrs | My Summary | Logout

INDUSTRIAL SCIENTIFIC

Equipment
View my gas detector fleet and other equipment

Alarms
Review comprehensive gas alarm data

Users
Manage my users and recipients of email reports

Reports
Detailed reports of past activities

Health
View a dashboard indicating the health of gas detection program

Search: Equipment Go

All times are shown in the GMT-05:00 Eastern Time (US & C...
inet - © 2005-2018 Industrial Scientific Corporation

Privacy Policy View Mobile



YOUR PEOPLE
**BACK HOME AT THE
END OF EVERY SHIFT**

ONE DOCKING STATION **THREE MODES**

Choose the out-of-the-box solution that best fits your needs.

WHERE DO YOU WANT **YOUR DATA?**

DSX

STANDALONE




DSXi

CLOUD-CONNECTED



DSX-L

LOCAL SERVER



DSX

STANDALONE



The DSX in standalone mode is a simple out-of-the-box gas detector maintenance station that requires no PC or network configuration.

- Easy bump testing and calibration of instruments upon dock.
- Automated record keeping with direct USB data storage eliminates concerns about storage space or losing compliance data.
- Automatic printing of bump and calibration certificates (with direct connect printer) provides hardcopy printouts for hot work and confined space entry.
- Automatic instrument wake-up and battery charging.
- Auto detection of calibration gas type and expiration date upon cylinder connection.



With the use of a DSXi activation key, the DSX Standalone becomes a cloud-connected fully automated instrument maintenance station. There is no need to send anything back for activation – all upgrades are easily performed in the field.

DSXi

CLOUD-CONNECTED



The DSX in cloud-connected mode is an automated maintenance, record storage, and fleet management solution.

- Bump test and calibration schedules can be tracked and set to be performed automatically, ensuring that instruments are ready for use prior to the start of a shift.
- Cloud-based data storage provides peace of mind with automatic file back-up, and easy recovery in case of unexpected data loss.
- Effortlessly manage your fleet, data, and software updates from any web-enabled device.
- Email alerts and notifications provide information on worker exposure and instrument usage, as well as instrument service needs.
- Stop worrying about calibration gas. The optional auto calibration gas replenishment program provides an efficient way to manage your calibration gas usage and needs. New cylinders will be shipped to you when you need them.

DSX-L

LOCAL SERVER



The DSX in local server mode provides the option to automatically store data from all docking stations behind a corporate network firewall, addressing network and data storage restrictions or preferences.

- Bump test and calibration schedules can be tracked and set to be performed automatically, ensuring that instruments are ready for use prior to the start of a shift.
- Automatic instrument wake-up and battery charging.
- Company and application specific instrument settings are easily set up from within the company network.
- Configure reports to provide the data you want, when you want it.
- Calibration gas status indicators provide warning to order replacement gas before a cylinder is empty.

WHAT'S YOUR MODE?

	 Standalone	 Cloud-connected	 Local Server
Record Storage	USB	Cloud	PC, Server
Bump and Cal	✓	✓	✓
Print Certificates	✓	✓	✓
6-Ports (Optional)	✓	✓	✓
Reports		✓	✓
Fleet Management		✓	✓
Event Scheduling		✓	✓
Email Alerts		✓	
Auto Software Updates		✓	
Auto Cal Gas Replenishment (Optional)		✓	
Price	\$	\$\$	\$\$\$
Software	Not Applicable	Included	Included

ORDERING INFORMATION

PART NUMBER

DESCRIPTION

INSTRUMENT CONFIGURATIONS

18109327-ABC	Ventis™ MX4
18109328-ABC	Ventis™ LS
18109329-ABC	MX6 iBrid™
18109330-ABC	Tango™ TX1
18109331-ABC	GasBadge® Pro
-ABC	A – DSX Mode: 0 = DSX Standalone 1 = DSXi Cloud-connected 2 = DSX-L Local Server B – Number of Gas Inlet Ports: 3 = 3 Ports 6 = 6 Ports C – Power Cord Type: 0 = None 1 = North America 2 = Europe 3 = Australia 4 = UK

KITS*

18109400	DSX Standalone Kit: Tango TX1 (H ₂ S)
18109401	DSX Standalone Kit: Ventis MX4 (LEL, CO, H ₂ S, O ₂)
18109404	DSXi Cloud-connected Kit: Tango TX1 (H ₂ S)
18109405	DSXi Cloud-connected Kit: Ventis MX4 (LEL, CO, H ₂ S, O ₂)

ACCESSORIES

18105684	iGas® Reader
18105924	5-Port Gas Regulator Manifold Clamp
18105932	6-Port Gas Regulator Manifold
17113887	Ethernet Cable, 5' (Cat5E network cable)
17113895	Ethernet Cable, 10' (Cat5E network cable)
17113903	Ethernet Cable, 25' (Cat5E network cable)
17154813	3G / 4G Router
17113945	5-Port Ethernet Hub
18109406	DSX to DSXi Activation Certificate

PHYSICAL SPECIFICATIONS

WARRANTY

Two-year warranty – DSX (Standalone) and DSX-L (Local Server)
Guaranteed For Life™ Program** – DSXi (Cloud-connected)

INSTRUMENTS SUPPORTED

GasBadge Pro, MX6 iBrid, Tango TX1, Ventis MX4, Ventis LS

DIMENSIONS

GasBadge Pro, Tango TX1: H: 22.7cm (8.92"); W: 16.9cm (6.65"); D: 27.3cm (10.75")

Ventis MX4, Ventis LS: H: 24.9cm (9.83"); W: 16.9cm (6.65"); D: 27.3cm (10.75")

MX6 iBrid: H: 25.3cm (9.96"); W: 16.9cm (6.65"); D: 27.3cm (10.75")

GAS INLETS

3-Port Version: One "fresh" air port, two calibration gas ports

6-Port Version: One "fresh" air port, five calibration gas ports

PUMP FLOW RATE

1.2 SCFH (550 mL / min)

COMMUNICATION

10 / 100 Ethernet support, RJ-45 Category 5 Connection

DISPLAY

128 x 64 Dot Matrix LCD – Multilingual modes

English, Spanish, French, German and Portuguese***

PERFORMANCE SPECIFICATIONS

OPERATING TEMPERATURE RANGE

0 °C to +50 °C / 32 °F to 122 °F

OPERATING HUMIDITY RANGE

0% to 80% relative humidity (RH) up to 30 °C (86 °F), decreasing linearly to 50% RH at 50 °C (122 °F)

EXTERNAL POWER SUPPLY RATINGS

Supply voltage: 100-240 VAC / 12 VDC

Frequency range: 50-60 Hz

Current rating: 5A

***DSX Docking Station Kits Include:** Choice of Standalone or Cloud-connected 3-port DSX Docking Station, 116L calibration gas (appropriate mix) with demand flow regulator with iGas® pressure switch, USB storage device (Standalone only).

**Specific terms of the Guaranteed for Life™ Program are included with all products and are available upon request.

***DSX-L (Local Server) does not support Portuguese.

INDUSTRIAL
SCIENTIFIC

www.indsci.com/dsx

AMERICAS

Phone: +1-412-788-4353 | Fax: +1-412-788-8353
1-800-DETECTS (338-3287) North America
info@indsci.com

ASIA PACIFIC

Phone: +65-6561-7377
Fax: +65-6561-7787
info@ap.indsci.com

EMEA

Phone: +33 (0)1 57 32 92 61
Fax: +33 (0)1 57 32 92 67
info@eu.indsci.com