



Flammable Safety Cabinets

- Sturdy all welded 16 gauge double wall steel construction
- Choice of manual or self closing doors
- 2" wide louvers support shelves, adjustable on 4" centers
- 2" Deep leak proof base
- Safely contains hazardous chemicals reducing the risk of fire
- Units come fully assembled and ready for use
- Electrical ground on bottom right hand side to aid in the elimination of an electrostatic discharge
- Improved security with recessed lockable paddle latch and 3 point locking system
- Bunged air vents on each side of the cabinet allows for ventilation
- Safety yellow powder coat finish

Model	Capacity (gl.)	Overall Dim: WxDxH (in.)	Shelves	Optional Shelf Part	Door Style	Ship Wt. (lbs.)
491M60	2	17-3/8 x 18-1/8 x 17-1/4	1	FS-SH-1413	Manual	70
491M61	2	17-3/8 x 18-1/8 x 18-3/8	1	FS-SH-1413	Self Closing	79
45AE90	4	17-3/8 x 18-1/8 x 22-1/8	1	FS-SH-1413	Manual	104
45AE83	4	17-3/8 x 18-1/8 x 23-3/8	1	FS-SH-1413	Self Closing	110
491M59	24 Aerosol cans	23 x 18 x 35	2 Slide Shelves	-	Manual	170
45AE84	12 - Horizontal	43 1/8 x 18 1/8 x 18 1/8	1	FS-SH-1439	Manual	165
45AE87	12	23 x 18 x 36-3/8	1	FS-SH-1419	Self Closing	167
491M63	16	23 x 18 x 45 3/8	1	FS-SH-1419	Self Closing	194
491M64	22	23-5/16 x 18-1/8 x 65	2	FS-SH-1419	Manual	283
45AE81	22	23-5/16 x 18-1/8 x 66-3/8	2	FS-SH-1419	Self Closing	296
491M65	22	35 x 22 x 35	1	FS-SH-1731	Manual	240
491M66	22	35 x 22 x 35	1	FS-SH-1731	Self Closing	244
491M67	24	23-5/16 x 18-1/8 x 65	3	FS-SH-1419	Manual	302
491M70	24	23-5/16 x 18-1/8 x 66-3/8	3	FS-SH-1419	Self Closing	316
491M69	24	43 x 12 x 44	3	FS-SH-0839	Self Closing	278
491M68	30 - Paint & Ink	43 x 12 x 65	5	FS-SH-0839	Manual	372
45AE86	30	43 x 18 x 45-3/8	1	FS-SH-1439	Self Closing	309
491M78	30	43 x 12 x 65	5	FS-SH-0839	Self Closing	386
491M71	45	43 x 18 x 65	2	FS-SH-1439	Manual	409
45AE88	45	43 x 18 x 66-3/8	2	FS-SH-1439	Self Closing	423
491M76	55 - Drum	34 x 34 x 65	1	FS-SH-2930	Manual	501
491M75	55 - Drum	34 x 34 x 66-3/8	1	FS-SH-2930	Self Closing	528
491M73	60	43 x 18 x 65	5	FS-SH-1439	Manual	423
45AE82	60	34 x 34 x 66-3/8	2	FS-SH-2930	Self Closing	533
491M74	60	43 x 18 x 66-3/8	5	FS-SH-1439	Self Closing	443
45AE85	90	43 x 34 x 65	2	FS-SH-2939	Manual	587
45AE89	90	43 x 34 x 66-3/8	2	FS-SH-2939	Self Closing	623



Red Flammable Safety Cabinets

- Sturdy all welded 16 gauge double wall steel construction
- Choice of manual or self closing doors
- 2" wide louvers support shelves, adjustable on 4" centers
- 2" Deep leak proof base
- Safely contains hazardous chemicals reducing the risk of fire
- Units come fully assembled and ready for use
- Electrical ground on bottom right hand side to aid in the elimination of an electrostatic discharge
- Improved security with recessed lockable paddle latch and 3 point locking system
- Bunged air vents on each side of the cabinet allows for ventilation
- Safety red powder coat finish

Model	Capacity (gl.)	Overall Dim: WxDxH (in.)	Shelves	Optional Shelf Part	Door Style	Ship Wt. (lbs.)
491M89	30	43 x 18 x 44	1	FS-SH-1439	Manual	285
491M94	30	43 x 18 x 45-3/8	1	FS-SH-1439	Self Closing	309
491M97	45	43 x 18 x 65	2	FS-SH-1439	Manual	409
491M98	60	34 x 34 x 65	2	FS-SH-2930	Manual	509
491M99	60	34 x 34 x 66-3/8	2	FS-SH-2930	Self Closing	533






491M88
Holds 4 gas cylinders



491M90
Holds 8 gas cylinders



491M77
Holds 12 gas cylinders



491M91
Holds 16 gas cylinders

Horizontal Cylinder Storage Cabinets

- 1-1/2" x 1/8" angle iron frame
- Solid 14-gauge steel top and bottom
- Expanded metal sides, back and door, for ventilation and visibility of contents
- Cylinder cradles securely hold propane tanks in place
- DANGER FLAMMABLE MATERIALS signs on doors
- Pre-punched lagging holes in feet

- Heavy duty butt hinges prevent door sagging
- Door has pad-lock hasp to secure contents (pad-lock not furnished)
- Magnet keeps door safely shut when not locked
- In full compliance with OSHA and NFPA standards when used properly
- Ships fully assembled
- Durable safety yellow powder coat finish

Model	Overall Dim: WxDxH (In.)	Cylinder Type	Ship Wt. (Lbs.)
491M88	30-1/8 x 29-3/4 x 34-7/8	20 lb. and 33-1/2 lb. LPG cylinders	127
491M90	30-3/16 x 30-13/16 x 71-7/8	20 lb. and 33-1/2 lb. LPG cylinders	193
491M77	41-15/16 x 51-5/8 x 71-7/8	50 lb. cylinders	370
491M91	30 x 59-3/4 x 71-7/8	20 lb. and 33-1/2 lb. LPG cylinders	354
Self-closing models			
491M85	30-1/4 x 31-7/8 x 54-3/4	20 lb. and 33-1/2 lb. LPG cylinders	169
491M86	42 x 51-3/4 x 71-7/8	50 lb. cylinders	370
491M87	30-1/4 x 61-1/2 x 71-7/8	20 lb. and 33-1/2 lb. LPG cylinders	355



491M92
Holds 9 vertical & 8 horizontal gas cylinders

Combination Horizontal/Vertical Cylinder Storage Cabinet

- 1-1/2" x 1/8" angle iron frame
- Solid 14-gauge steel top and bottom
- Expanded metal sides, back and door, for ventilation and visibility of contents
- Accepts all standard vertical cylinders up to 59-3/4" tall plus 20 Lb. and 33-1/2 lb. cylinders in the horizontal compartment
- Vertical compartment includes a chain, adjustable in 1" increments, to hold cylinders in place
- Pre-punched lagging holes in feet
- on doors
- Heavy duty butt hinges prevent door sagging
- Doors have pad-lock hasp to secure contents (pad-lock not furnished)
- Magnet keeps door safely shut when not locked
- In full compliance with OSHA and NFPA standards when used properly
- Ships fully assembled
- Durable safety yellow powder coat finish
- DANGER FLAMMABLE MATERIALS signs

Model	Overall Dim: WxDxH (In.)	Cylinder Capacity	Ship Wt. (Lbs.)
491M92	59-3/4 x 30 x 71-3/4	9 vertical & 8 horizontal	310



491M93
Holds 2 gas cylinders



491M79
Holds 4 gas cylinders



491M95
Holds 9 gas cylinders



491M96
Holds 18 gas cylinders

Vertical Cylinder Storage Cabinets

- 1-1/2" x 1/8" angle iron frame
- Solid 14-gauge steel top and bottom
- Expanded metal sides, back and door, for ventilation and visibility of contents
- Cylinder cradles securely hold propane tanks in place
- DANGER FLAMMABLE MATERIALS signs on doors
- Pre-punched lagging holes in feet

- Heavy duty butt hinges prevent door sagging
- Door has pad-lock hasp to secure contents (pad-lock not furnished)
- Magnet keeps door safely shut when not locked
- In full compliance with OSHA and NFPA standards when used properly
- Ships fully assembled
- Durable safety yellow powder coat finish

Model	Overall Dim: WxDxH (In.)	Cylinder Type	Ship Wt. (Lbs.)
491M93	20-1/4 x 31-3/16 x 35	50 lb. cylinders	87
491M79	30-1/8 x 29-3/4 x 34-7/8	50 lb. cylinders	100
491M95	30 x 29-3/4 x 71-3/4	standard up to 59-3/4" tall	141
491M80	30-3/16 x 49 x 71-7/8	standard up to 59-3/4" tall	254
491M96	30 x 60 x 71-27/32	standard up to 59-3/4" tall	254
491M81	30-3/16 x 73 x 71-7/8	standard up to 59-3/4" tall	291
Self-closing models			
491M82	30-1/4 x 31-7/8 x 35	50 lb. cylinders	100
491M83	30-1/4 x 49-1/2 x 71-7/8	standard up to 59-3/4" tall	254
491M84	30-1/4 x 61-1/2 x 71-7/8	standard up to 59-3/4" tall	254

Condor gas cylinder storage cabinets are designed and constructed in full compliance with OSHA and NFPA standards for the storage of gas cylinders only. All compressed gases must be used in accordance with OSHA regulations and the Compressed Gas Association's (CGA) Pamphlets which have been adopted by OSHA regulations by reference.

For proper storage, handling and maintenance of compressed gas cylinders, please consult Compressed Gas Association Pamphlet P-1 and U.S. Department of Labor, OSHA General Industry standard 29 CFR 1910.101 which adopts by reference the Compressed Gas Association's (CGA) Pamphlets C-6-1986, C-8-1962, and P-1-1965. The Compressed Gas Association has updated the three pamphlets cited by OSHA as C-6-1993, C-8-1997, and P-1-1999.

Compressed gases should only be handled by experienced and properly trained people. [CGA 3.4.1]
Condor gas cylinder storage cabinets are for the storage of gas cylinders only.

Call or visit your local branch or go to grainger.com/condor for complete product line information.

