

Scotch-Brite™ Roloc™ Body Man's Bristle Disc PN 07536



Removes High Loading
Materials Fast
Doesn't Load



Scotch-Brite™ Roloc™ Body Man's Bristle Disc, PN 07536, combines a very unique bristle design with a new polymer formulation, enabling it to remove high loading substrates (rubberized undercoating, seam sealers, rust and paint) quickly, while maintaining product life.





UPC	Size	Color	Grade/Scratch Equivalent	Application
051131-07536	2"	Purple Signifies "Best In Class"	36/80	Use to remove rubberized undercoating, seam sealers, rocker panel coatings, rust and paint quickly without loading. Abrades surface to bare metal.

UPC	Diameter	Description	Shaft Size	Provides firm support for Scotch-Brite™ Surface Conditioning Discs.
051144-05539	2"	3M™ Roloc™ Disc Pad Assembly	¼" Diameter	Pad assembly comes complete with 2" 3M Roloc Disc Pad, 2" steel shaft, and 7/16-20 adaptor.

WHY USE SCOTCH-BRITE™ ROLOC™ BODY MAN'S BRISTLE DISCS?

Features	Advantages	Benefits
Unique bristle design	Resists loading and clogging when removing high loading substrates	Effective/ Works fast
New polymer formulation	Stiffer bristles for longer life	Efficient/ Saves money/reduces waste
3M Roloc Attachment System	Scotch-Brite™ Roloc™ disc locks securely ½ turn on, ½ turn off	Saves Time/ Easy to use
3M Roloc Disc Pad Assembly designed to fit a variety of tools with or without collets or chucks	Ideal for use on right angle or straight shaft air tools	Versatile
Scotch-Brite Roloc Body Man's Bristle Disc contains no wire filaments	Potential for injury from flying wires is eliminated	Technician Safety

ORDERING INFORMATION

UPC	Description	Qty/Box	Boxes/Case
051131-07536	Scotch-Brite Roloc Body Man's Bristle Disc, PN 07536, 2"	4 Discs	6
051144-05539	3M Roloc Disc Pad Assembly – 2"	1	10

Important Notice to Purchaser

Safety Information: Always read and follow all safety information included with the product. Do not exceed maximum operating RPM's. Use guards provided with machine. Follow safety operation procedures posted in work areas.

Product Use: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can effect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environments conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy: Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability: Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence, or strict liability.



Industrial & Transportation Business
 Building 21-1W-10
 900 Bush Avenue
 St. Paul, MN 55144-1000

3M, Scotch-Brite and Roloc are trademarks of 3M © 2007

61-5002-8144-1