


NOT for Patient-Care Rooms - UL1363 Hospital-Grade Surge Protector with 6 Hospital-Grade Outlets, 15 ft. Cord, 1050 Joules

MODEL NUMBER: **SPS-615-HG**



Highlights

- 6 hospital-grade outlets
- 1050 joule rating
- 15-ft. cord with molded hospital-grade plug
- All metal housing

Package Includes

- SPS-615-HG Surge Suppressor
- Instruction manual with warranty information

Description

Tripp Lite's SPS-615-HG offers 15A-capacity AC surge suppression and power distribution in a rugged all-metal outlet strip for 120V applications. Offers 6 AC outlets, 15-ft. AC power cord, built-in resettable circuit breaker and 1050-joule AC surge suppression. Features safety-enhanced hospital grade plug and outlets. Switch safety cover prevents accidental shutoff. Optional use keyhole mounting tabs. 15A circuit breaker controls power to all outlets and protects against overloads. LED indicator verifies line power available. PLUG/OUTLETS: NEMA 5-15PHG Hospital-Grade Plug and 6 x NEMA 5-15RHG Hospital-Grade AC Outlets

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: All-metal corded multi-outlet surge suppression strip

SUPPRESSION: AC: 150V RMS Clamping/1050 joules

Features

- 1050-joule AC surge suppression rating
- Rugged all-metal housing withstands years of use without loss of ground path continuity
- 6 NEMA5-15R Hospital-Grad AC outlets
- 15-ft. AC cord with integrated, molded Hospital-Grade NEMA 5-15PHG plug
- Keyhole mounting tabs and flanges
- Switch safety cover prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120 volt, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)
- UL1449 3rd Edition listed
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required



Specifications

OVERVIEW	
UPC Code	037332100085
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	19500
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	LINE POWER PRESENT (green)
Locking Switch Cover	Locking switch cover
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode surge suppression
Clamping Voltage (RMS)	140
Automatic Shut-Off	Yes



DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Anti-Microbial Protected	Yes
Color	White
Color (AC Line Cord)	Light Gray
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Metal
Receptacle Color	White
Shipping Dimensions (hwd / cm)	37.59 x 5.59 x 16.00
Shipping Dimensions (hwd / in.)	14.80 x 2.20 x 6.30
Shipping Weight (kg)	1.32
Shipping Weight (lbs.)	2.90
Unit Dimensions (hwd / cm)	3.81 x 34.9 x 6.35
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Weight (kg)	1.45
Unit Weight (lbs.)	3.20
SPECIAL FEATURES	
Rotatable Outlets	No
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition (Series Number: AGIB12015SL)
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
Canada	cUL (Series Number: AGIB12015SL)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>