



ELEMENT SPECS		
PART NUMBER	848	
MATERIAL	Paper	
FLOW RATE	115 CFM	195 m ³ /hr
SURFACE AREA	5.0 ft ²	0.5 m ²
I.D.	2.57"	65mm
O.D.	5.00"	127mm
HEIGHT	4.75"	121mm