



BACKPACK VACUUMS



Product Specifications

FEATURES	SPECIFICATIONS	
Product Name	Aspen™-6	Aspen™-10
TECHNICAL REQUIREMENTS		
Vacuum Motor		
Vac Motor Power	1200W	1200W
Vac Motor Current	10 amps	10 amps
Vacuum Motor hp	1.6 hp / 1.19 kW	1.6 hp / 1.19 kW
Vac Motor Airflow	111 CFM	111 CFM
Vac Motor Sealed Water Lift	119 in / 3023 mm	119 in / 3023 mm
Vac Motor Thermal Protection	Thermal protector w/ manual reset required	Thermal protector w/ manual reset required
Filtration		
HEPA Filter, Standard	99.97% @ 0.3 micron	99.97% @ 0.3 micron
Vacuum Bag		
Vacuum Bag	Paper bag is standard	Paper bag is standard
Easy to Change Vac Bag	Two over-center latches	Two over-center latches
Vacuum Capacity	6 qt / 5.7 L	10 qt / 9.5 L
Body / Frame		
Harness	Deuter® with 27-54 in / 686-1372 mm adjustability	Deuter® with 27-54 in / 686-1372 mm adjustability
Weight	13.0 lbs / 5.9 kg (10 lbs / 4.5 kg body, 3 lbs / 1.4 kg harness) Total weight without cord	13.5 lbs / 6.1 kg (10.5 lbs / 4.8 kg body, 3 lbs / 1.4 kg harness) Total weight without cord
Dimensions	H: 21 in / 533 mm (25 in / 635 mm with harness) W: 9.5 in / 241 mm (11 in / 279 mm with harness) D: 7 in / 178 mm (10 in / 254 mm with harness)	H: 25 in / 635 mm (27 in / 686 mm with harness) W: 9.5 in / 241 mm (11 in / 279 mm with harness) D: 7 in / 178 mm (10 in / 254 mm with harness)
Electrical / Power		
Power Cord Connection	Kettle plug w/ additional restraint bracket	Kettle plug w/ additional restraint bracket
On/Off Switch	Tethered On/Off switch affixed on the hip belt	Tethered On/Off switch affixed on the hip belt
Power Cord Length	Length: 50 ft / 15m Plug end: NA Color: Yellow	Length: 50 ft / 15m Plug end: NA Color: Yellow
Electrical Input	120 V / 50-60 Hz	120 V / 50-60 Hz
Vacuum Hose		
Hose Length	2-6 ft / 0.61-1.80 m Stretch hose Included with vacuum	2-6 ft / 0.61-1.80 m Stretch hose Included with vacuum
Hose Diameter @ wand	1.50 in / 38 mm	1.50 in / 38 mm

Product Specifications (continued)

FEATURES	SPECIFICATIONS	
Product Name	Aspen-6	Aspen-10
TECHNICAL REQUIREMENTS (cont.)		
Wand & Tools		
Base Kit	- Two piece locking S-wand, Aluminum - 14 in / 356 mm carpet tool w/bumper - 14 in / 356 mm nylon fill floor brush - 1.50 in / 38 mm components	- Two piece locking S-wand, Aluminum - 14 in / 356 mm carpet tool w/bumper - 14 in / 356 mm nylon fill floor brush - 1.50 in / 38 mm components
Standard Kit	- Chrome telescopic S-wand - 14 in / 356 mm carpet tool w/bumper - 14 in / 356 mm nylon fill floor brush - 1.50 in / 38 mm components	- Chrome telescopic S-wand - 14 in / 356 mm carpet tool w/bumper - 14 in / 356 mm nylon fill floor brush - 1.50 in / 38 mm components
Premium Kit	- Two piece 59 in / 1499 mm anodized aluminum wand - 18 in / 457 mm Sidewinder® carpet tool - 18 in / 457 mm Sidewinder® nylon floor brush - 1.50 in / 38 mm components	- Two piece 59 in / 1499 mm anodized aluminum wand - 18 in / 457 mm Sidewinder® carpet tool - 18 in / 457 mm Sidewinder® nylon floor brush - 1.50 in / 38 mm components
Anti-static machine	Anti-static performance	Anti-static performance
Max CRI Rating*	CRI Gold with high performance tool	CRI Gold with high performance tool
Sound Level		
Sound pressure test (per IEC-60335-2-69 section EE.2.1)	67 dBA	67 dBA
REGULATORY / SAFETY		
US & Canada (UL listed**) 	Yes	Yes
Mexico (NOM) 	Yes	No
AFTERMARKET PARTS		
Kit, Harness hip extension	Enable extension length to 72 in / 1829 mm	Enable extension length to 72 in / 1829 mm
Tool Accessory Kit	- 5 in / 127 mm natural fill dusting tool - 5 in / 127 mm upholstery tool - 15 in / 381 mm crevice tool - 1.50 in / 38 mm components	- 5 in / 127 mm natural fill dusting tool - 5 in / 127 mm upholstery tool - 15 in / 381 mm crevice tool - 1.50 in / 38 mm components

** See CRI website for qualified tools for all competitors

*** Tested to the UL standard

Specifications are subject to change without notice

Deuter® is a registered trademark of Deuter Sport GMBH

Sidewinder® is a registered trademark of JanPro Products