

# 48 11 J0

## Precision Circlip Pliers to assemble internal circlips into bores



- heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- joint with screw: precise, zero-backlash operation of pliers
- non-slip plastic coating on the handles
- Pliers body: chrome vanadium electric steel, forged, oil-hardened
- Inserted tips: spring steel wire, drawn
  - Style: DIN 5256 C, straight tips



Easy and reliable assembly: form-fitting inserted and pressed-in tips made of high-density spring steel offer a high level of protection against excessive stress and strain, e.g. when removing stuck rings. The large supporting surfaces and the position of the tips make it more difficult for the rings to bounce off.

High-density spring steel with a score-free surface is used for the tips. This increases the tips' resistance to dynamic and static strain. The tips are 30% more stable than conventional pliers when subjected to one-off overloading while still allowing good accessibility during assembly. Subjected to dynamic strain, the tips' resistance capacity is up to 10 times greater! The tips on the precision circlip pliers are non-detachable!

|                          |                               |
|--------------------------|-------------------------------|
| <b>Product Number</b>    | 48 11 J0                      |
| <b>EAN</b>               | 4003773048510                 |
| <b>Pliers</b>            | grey atramentized             |
| <b>Handles</b>           | with non-slip plastic coating |
| <b>Style</b>             | 1                             |
| <b>Size of bore Ø mm</b> | 8 - 13                        |
| <b>Tips Ø mm</b>         | 0,90                          |
| <b>Length mm</b>         | 140                           |
| <b>Net weight g</b>      | 105                           |




Sturdy, inserted tips: made from high-density spring steel



slim head shape



Screw joint: high precision and optimum drive



Tight fit through compression

technical change and errors excepted

