



9399

Cut Protection Specification Sheet

PRODUCT DESCRIPTION:

Cut to the chase! Excellent Cut Protection found Here! the 9399 Combines DuPont™ Kevlar® and Stainless Steel construction to deliver excellent cut resistance. Material also offers a breathability that keeps hands cool and comfortable making them easier to wear for extended periods of time.

FEATURES:

- Combines DuPont™ Kevlar® and Stainless Steel construction
- 7 Gauge Kevlar® / Stainless Steel Material
- Comfortable and Cool
- Reinforced Thumb Crotch for added wear
- ANSI Cut Level 4


APPLICATIONS:

Automotive Assembly, Canning, Food service, HVAC, Warehousing



TECHNICAL DATA FOR: 9399

Material Group	Strings
Product Type	Cut Protection
Glove Size	Large
Gauge	7 Gauge
Material	Kevlar





MCR
SAFETY

9399

Cut Protection Specification Sheet

Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9399L	Large	9.750	4.375	N/A	1.212 lb.	0.101
9399M	Medium	0	0	N/A	1.224 lb.	0.102
9399S	Small	9.500	4.064	N/A	0.996 lb.	0.083
9399XL	X - Large	0	0	N/A	1.296 lb.	0.108
9399XXL	XX - Large	0	0	N/A	1.200 lb.	0.100

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved