

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-531

Palm-Dipped with INTERCEPT TECHNOLOGY® and ANSELL GRIP™ Technology



Cut



Light Duty

Lightweight cut-resistant industrial gloves with strong, long-lasting grip

- **Enhanced grip:** Patented ANSELL GRIP™ Technology and palm-dipped coating strengthen these safety gloves' grip
- **Elevated comfort:** ZONZ™ Comfort Fit Technology, with special yarn and stitching design, allows for simpler hand movement and reduced hand fatigue
- **Lightened feel:** HyFlex® 11-531 industrial safety gloves' lightweight liner means flexible, maneuverable hand protection
- **Improved durability:** FORTIX™ Abrasion Resistance coating ensures HyFlex® 11-531 industrial working gloves remain abrasion-resistant
- **Heightened protection:** INTERCEPT™ Cut Resistance Technology provides basic cut protection
- **Considered aesthetics and practicality:** Palm-based dirt masking hides stains, while HyFlex® 11-531 PPE gloves also come in vend pack form

Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges
- Assembly & inspection of components
- Applying finish to materials, products



HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-531

Palm-Dipped with INTERCEPT TECHNOLOGY[®] and ANSELL GRIP[™] Technology

Key Features

- Palm-dipped nitrile coating: Enhanced grip, for secure handling
- ZONZ[™] Comfort Fit: Fitted and breathable, with minimal hand fatigue
- Lightweight liner: PPE gloves that feel light and maneuverable

Technologies



DMF free



Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex [®] 11-531	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Fiber glass, Nylon, HPPE, Spandex Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	210-254 mm; 8.26-10.62 inches	Black	12 pairs in a bag, 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

