

## Exceptional Grip in Wet and Dry Environments

- Excellent splash protection against a broad array of chemicals
- Tested for use with chemotherapy/cytotoxic drugs
- Neoprene formulation and textured fingertips provides a secure grip
- Polymer coated for easy donning



### Industries

- Life Sciences
- Chemical
- Healthcare

### Recommended For

- Loading centrifuges and chromatography columns
- Assembly of parts
- Sample taking and processing
- Blending, compounding solids and liquids
- Administering drugs
- Testing
- Maintenance
- Tested for use with chemotherapy drugs
- Enhanced grip in wet environments
- Damp donning
- Higher-risk clinical applications
- Protection from Type I latex allergy in HCW's or patients



## TECHNICAL DATA SHEET

### PRODUCT INFORMATION

|  |  |
|--|--|
|  | <b>NeoPro<sup>®</sup> NPG-888</b>  |
| <b>Material</b>                          | Neoprene (Polychloroprene)   |
| <b>Color</b>                             | Green  |
| <b>Glove Design</b>                      | Polymer Coated, Powder-Free, Textured Fingers  |
| <b>Cuff</b>                              | Beaded   |
| <b>Manufacturing/QMS Audit Standards</b> | EN ISO 13485:2012  |
| <b>Regulatory/Standards Compliance</b>   | ASTM D6977, EN 420:2003 + A1:2009, US QSR/FDA 510(k) Medical Examination Grade                           |
| <b>Packaging</b>                         | 100 gloves per dispenser 10 dispensers per case 1000 gloves per case                                     |
| <b>Storage</b>                           | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition. |
| <b>Country of Origin</b>                 | Indonesia  |
| <b>User Needs Segment</b>                | Robust   |
| <b>Available sizes</b>                   | XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)                                       |
| <b>Anti-static</b>                       | Yes  |

### PHYSICAL PROPERTIES

|   | Typical Values      |                    | Testing Method      |
|---|---------------------|--------------------|---------------------|
| Length (mm/inches)                      | 245 / 9.6           |                    | ASTM D3767,EN 420   |
| Freedom from Holes (Inspection level I) | 1.5 AQL             |                    | ASTM D5151,EN 455-1 |
| Palm Thickness (mm/mils)                | 0.13 / 5.1          |                    | ASTM D3767,EN 420   |
| Finger Thickness (mm/mils)              | 0.17 / 6.7          |                    | ASTM D3767,EN 420   |
|   | <b>BEFORE AGING</b> | <b>AFTER AGING</b> |                     |
| Ultimate Tensile Strength (MPa)         | ≥ 24                | ≥ 18               | ASTM D412 & D573    |
| Elongation at Break (%)                 | ≥ 650               | ≥ 400              | ASTM D412           |
| Force at break (N)                      | ≥ 9                 | ≥ 9                | ASTM D6977          |

### ORDERING INFORMATION

| Size                | XS (5.5 - 6) | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) | XL (9.5 - 10) |
|---------------------|--------------|-------------|-------------|-------------|---------------|
| <b>Product Code</b> | NPG-888-XS   | NPG-888-S   | NPG-888-M   | NPG-888-L   | NPG-888-XL    |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Russia

Ansell PYC  
Ten. +7 495 258 13 16

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.