



Nitrile

## Durable nitrile gloves that offer extra durability to enhance safety

- Superior strength and durability for maximum protection against rips, snags or tears
- Low, 0.65 AQL for advanced barrier protection
- Tested for use with chemotherapy/cytotoxic drugs
- Meets or exceeds the emergency medical glove requirements of NFPA 1999
- Tested against both fentanyl and gastric acid (vomit) to simulate hazardous, real world overdose situations



### Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Healthcare

### Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Picking and fastening components
- Equipment repair and maintenance
- General Purpose Auto Aftermarket
- Tire rotation & changes
- Animal care feeding and cleanup
- Maintaining lab furniture and equipment
- Sample taking and processing
- Administering drugs
- Raw material sample collection
- Tested for use with chemotherapy drugs
- Extra protection over the wrist and arm
- Higher-risk clinical applications
- Protection from Type I latex allergy in HCW's or patients



### TECHNICAL DATA SHEET

#### PRODUCT INFORMATION

	<b>Supreno® EC SEC-375</b>
<b>Material</b>	Nitrile
<b>Color</b>	Violet Blue
<b>Glove Design</b>	Chlorinated, Powder-Free, Textured Fingers
<b>Cuff</b>	Beaded
<b>Manufacturing/QMS Audit Standards</b>	ISO 13485:2003
<b>Regulatory/Standards Compliance</b>	ASTM D6319, EN 1149-1/2/3, EN 420:2003 + A1:2009, ISO 11193, ISO 13485, NFPA 1999:2013, US QSR/FDA 510(k) Medical Examination Grade
<b>Packaging</b>	50 gloves per dispenser; 10 dispensers per case; 500 gloves per case; *40 gloves per dispenser (Size XXXL) *400 gloves per case (Size XXXL)
<b>Storage</b>	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
<b>Country of Origin</b>	Malaysia
<b>User Needs Segment</b>	High Risk
<b>Available sizes</b>	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10), XXL (10.5 - 11), XXXL (11.5 - 12)
<b>Anti-static</b>	Yes

#### PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	295 / 11.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.14 / 5.5		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.22 / 8.7		ASTM D3767,EN 420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	30	27	ASTM D412 & D573
Elongation at Break (%)	≥500	≥400	ASTM D412
Force at break (N)	18	18	EN 455-2

#### ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)	XXXL (11.5 - 12)
<b>Product Code</b>	SEC-375-XS	SEC-375-S	SEC-375-M	SEC-375-L	SEC-375-XL	SEC-375-XXL	SEC-375-XXXL

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Russia

Ansell PYC  
Ten. +7 495 258 13 16

#### Performance Standards and Regulatory Compliance



ISO 13485

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.