



MAX PERFORMANCE
EXTREME HEAVY-DUTY
BUILT FOR STARTING



FULLY AUTOMATIC

BATTERY CHARGER ENGINE STARTER

FOR ADVANCED DIAGNOSTIC TESTING, ENGINE STARTING & CHARGING

SC1308



BATTERY TYPES:
STANDARD AGM
DEEP-CYCLE



ENGINE START

30A
BOOST

6 <-> 2A
CHARGE / MAINTAIN

100A ENGINE STARTER

POWERFUL ENOUGH FOR STARTING CARS, SUVs AND SMALL TRUCKS

MICROPROCESSOR CONTROLLED

AUTOMATICALLY ADJUSTS THE AMPERAGE RATE TO CHARGE & MAINTAIN.
MULTI-STAGE CHARGING FOR ADDED PRECISION, SAFETY & BATTERY LIFE.

BATTERY AND ALTERNATOR TESTER

PROVIDES CHARGE LEVEL AND HELPS DIAGNOSE ELECTRICAL PROBLEMS.

DIGITAL DISPLAY, LED INDICATORS AND BUTTON CONTROLS

FOR EASE AND ACCURACY

REVERSE HOOK-UP PROTECTION

CHARGER WILL NOT OPERATE IF CLAMPS ARE REVERSED.

FLOAT MODE MONITORING

AUTOMATICALLY MAINTAINS OPTIMUM BATTERY CHARGE

AUTO VOLTAGE DETECTION

AUTOMATICALLY DETECTS 6 OR 12 VOLT BATTERIES

SCHU ECO ENERGY

MEETS THE HIGHEST INDUSTRY STANDARDS FOR ENERGY EFFICIENCY.



MAXIMIZING
ENERGY EFFICIENCY
SUPERIOR PERFORMANCE