



# ***An industrial scale offering reliability, flexibility and repeatability***



## **Functions**



- Capacity 330 lbs. (150Kg)

## **Features**

- Optional display on mobile device with free iOS® or Android™ App
- High-contrast backlit LCD display
- High accuracy and repeatability
- Wireless range: 35 ft to 100 ft pending environmental conditions
- Programmable alarm (App only)
- Selectable units: English or Metric
- Lightweight, compact and durable frame
- Large size scale platform
- Overload protection: Min 150% max load
- No-slip platform surface
- Hoist clip access
- 1-Year limited warranty

## **Applications**

- Measuring refrigerant weights in english and metric units
- Charging HVAC systems
- Charging refrigeration systems, large and small
- Weighing recovered or transferred weight of refrigerant






### Includes

- Free App for iOS® and Android™
- Rechargeable batteries
- Battery charger cable
- Carrying pouch

### App "UEi Scale"



### Specifications

Model #	WRSX
	
Capacity (Load cell)	330 lbs (150 kg)
Accuracy	32° to 68° / 122° to 158°F 0 to 80 lbs (0 to 40kg) ±0.2% F.S. ±1 dgt
	32° to 68° / 122° to 158°F 80 to 330 lbs (40 to 150kg) ±0.6% F.S. ±1 dgt
	68° to 122°F 0 to 80 lbs (0 to 40kg) ±0.2% F.S. ±1 dgt
	68° to 122°F 80 to 330 lbs (40 to 150kg) ±0.3% F.S. ±1 dgt
Resolution	0.25 oz (7g)
Programmable alarm	•
Display	Backlit LCD
Wireless	•
35 ft wireless distance	•
IP (of electronics)	55
Free App	•
Large size platform (>10.5")	•
No-slip rubberized pad	•
Light weight	6.5 lbs
Compact	•
Power	Rechargeable Battery
Battery life	Min 100 hrs. between charges
Wireless compatibility	Bluetooth® 4.0 or newer

### Downloads



**Manual**



**Data Sheet**



Made in TAIWAN

Patent Pending