3MPolyester Film Tape 850

Product Description	3M TM Polyester Film Tape 850 can generally be used for splicing and applicate where chemical resistance and/or clean removal is necessary. The silver backing transparent polyester with a thin layer of aluminum.				
Product Construction	Backing A	dhesive	Color	Standard Roll Length	
	Polyester A	crylic	Transparent, Red, Black, White, Silver	72 yds. (65.8 m)	
Typical Physical Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. ASTM Test Method				
	Adhesion to Steel: Silver: Tensile Strength at Break: Elongation at Break: Backing Thickness: Total Thickness: Water Vapor Transmission Rate Silver	42 oz./in. wi 28 lbs./in. w 120% 0.9 mils (0.0 1.9 mils (0.0 2: 1.6 gms, H2 (24.8 g/m2/2 :: 0.9 gms, H2 (7.75 g/m2/2	05 mm) O/100 sq. in./24 hrs. 24 hrs.) O/100 sq. in./24 hrs.	D-3330 D-3330 D-3759 D-3759 D-3652 D-3652 D-3833	
Features	 and lose tensile strengt Thin, high strength pol meeting low caliper re- Chemical and solvent and solvent attack. 	h. yester film he quirements. resistance to h elp protect sur	elps reduce failures due to lelps reduce rejects produce	breakage while	

$3M^{TM}$ Polyester Tape 850

Application Ideas	 Transparent, Red, Black, White: Splicing and web defect marking. Sealing, labeling, and protecting. Positive film striping (transparent). Decorative edging. Tape hinge. 		
	 Silver: Post splicing movie film. Deflect flagging where reflective sensing is required. Decorative striping and die cutting. Decorative edging. 		
Storage	Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% relative humidity in the original packaging material.		
Shelf Life	To obtain best performance, use this product within 18 months from date of manufacture.		
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.		
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it if for a particular purpose and suitable for user's method or application.		
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3 warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITE TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOS OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTO OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy at 3M's option, replacement of the 3M product or refund of the purchase price.		

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



This Industrial Adhesives and Tapes Division product was manufactured under a quality system registered to ISO 9001:2000 standards.



Industrial Business Industrial Adhesives and Tapes Division 3M Center, Building 220-3S-06 St. Paul, MN 55144-1000 800-362-3550 · 577-369-2923 (Fax) www.3M.com/industrial

Recycled Paper 40% pre-consumer 10% post-consumer 3M is a trademark of 3M Company. Printed in U.S.A. ©3M 2012