

# CROSS X STEP


SERIES FXS1500

TYPE IA  
**300 lbs**  
 LOAD CAPACITY  
Includes weight of user plus materials


PRO TOP WITH "V" SHAPE TO FIT INTO CORNERS, INCLUDES MAGNET



RAPTOR BOOT- PROTECTS FIBERGLASS AND HAS NON-MARRING HEAVY DUTY BONDED TREAD



LOCKING LATCH TO SECURE REAR SECTION



SHOX- SUPERIOR IMPACT ABSORPTION, PROTECTS FIBERGLASS AND STEP



"H" BRACING MAKES IT EASY TO OPEN \*8, 10, 12 FT ONLY



DOUBLE RIVET & FLARED CONSTRUCTION FOR RIGIDITY AND STABILITY



**2 IN 1  
 LADDER**



\* Patent Pending



1-800-666-2811

www.LOUISVILLELADDER.com

MODEL	LADDER SIZE	BOTTOM WIDTH (IN)	APPROX. SPREAD (IN)	APPROX. WEIGHT (LBS)	APPROX. CUBES (FT)	SHEFLADDER		STEPLADDER	
						HIGHEST STANDING LEVEL (IN)	MAX. REACH	HIGHEST STANDING LEVEL (IN)	MAX. REACH
FXS1504	4'	20 3/4	24	15	4.0	11"	7' 6"	1' 11"	8' 6"
FXS1506	6'	23 3/4	36	21	6.8	2' 10"	9' 5"	3' 9"	10' 4"
FXS1508	8'	26 3/4	48	28	10.1	4' 9"	11' 4"	5' 8"	12' 3"
FXS1510	10'	29 3/4	60	39	14.0	6' 8"	13' 3"	7' 7"	14' 2"
FXS1512	12'	32 3/4	71	48	18.5	8' 6"	15' 1"	9' 6"	16' 1"

Check out the video on Youtube: <https://youtu.be/Qqd9IzYqbJM>

