

# EXTRA HEAVY DUTY FIBERGLASS TYPE IAA LADDERS [375LB CAPACITY]

## WW-3410 SERIES STEPLADDER

Item Number	Ladder Height	Max Reach	Max Standing Ht	Bottom Width	Base Spread	Approx Wt	Approx Cubes
44YY52	4'	8' 6"	1' 11"	19 ½"	29"	15 lbs.	3.2'
44YY48	6'	10' 4"	3' 9"	22 ½"	41"	21 lbs.	5.6'
44YY47	8'	12' 3"	5' 8"	25 ½"	52"	28 lbs.	8.4'
44YY37	10'	14' 2"	7' 7"	28 ½"	64"	42 lbs.	11.7'
44YY50	12'	16' 1"	9' 6"	31 ½"	76"	49 lbs.	15.4'



## WW-3430 SERIES STEPLADDER

Item Number	Ladder Height	Max Reach	Max Standing Ht	Bottom Width	Base Spread	Approx Wt	Approx Cubes
44YY09	4'	8' 6"	1' 11"	19 ½"	37"	19 lbs.	4.7'
44YY68	6'	10' 4"	3' 9"	22 ½"	52"	26 lbs.	8.1'
44YY16	8'	12' 3"	5' 8"	25 ½"	67"	37 lbs.	12.1'
44YY42	10'	14' 2"	7' 7"	28 ½"	82"	56 lbs.	16.9'
44YY24	12'	16' 1"	9' 6"	31 ½"	96"	72 lbs.	23.3'



# HEAVY DUTY FIBERGLASS TYPE IA STEPLADDERS [300<sub>LB</sub> CAPACITY]

**TYPE IA**

■ Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)



■ Equipped with slip-resistant boots that protect fiberglass and working surfaces (not available on 2' model)



■ Inside spreader braces and double rivet step construction for rigidity



■ ProTop™ Multiple tool slots to increase productivity



**ANSI**  
Meets or exceeds requirements of American National Standards Institute

44YY19

## WW-3010 SERIES STEPLADDER

Item Number	Ladder Height	Max Reach	Max Standing Ht	Bottom Width	Base Spread	Approx Wt	Approx Cubes
44YY34	2'	8' 4"	1' 11"	17"	18 1/8"	8 lbs.	1.98'
44YY63	4'	8' 4"	1' 11"	19"	28 1/4"	14 lbs.	1.79'
44YY19	6'	10' 4"	3' 10"	21 1/4"	40 3/8"	18 lbs.	5.19'
44YY29	8'	12' 3"	5' 8"	24 3/4"	52 1/2"	26 lbs.	8.02'
44YY61	10'	14' 2"	7' 7"	28"	64 3/4"	36 lbs.	11.31'
44YY30	12'	16' 1"	9' 6"	31"	77"	47 lbs.	15'

**SAFE** FOR USE AROUND ELECTRICITY

# HEAVY DUTY FIBERGLASS TYPE IA STEPLADDERS [300<sub>LB</sub> CAPACITY]

## TWIN FRONT LADDER

- Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)
- Both sides can be used simultaneously and hold up to 300 lbs. each
- Equipped with slip-resistant boots that protect fiberglass and working surfaces
- Inside spreader braces and double rivet step construction for rigidity
- Heavy gauge steel hinges on the top
- Meets or exceeds requirements of American National Standards Institute

### WW-3030 SERIES TWIN FRONT LADDER

Item Number	Ladder Height	Max Reach	Max Standing Ht	Bottom Width	Base Spread	Approx Wt	Approx Cubes
44YY54	4'	8' 6"	1' 11"	19 ½"	37"	18 lbs.	4.7'
44YY55	6'	10' 4"	3' 9"	22 ½"	52"	25 lbs.	8.1'
44YY38	8'	12' 3"	5' 8"	25 ½"	67"	33 lbs.	12.1'
44YY32	10'	14' 2"	7' 7"	28 ½"	82"	58 lbs.	16.9'
44YY33	12'	16' 1"	9' 6"	31 ½"	96"	62 lbs.	22.3'



**ANSI**  
Meets or exceeds requirements  
of American National Standards Institute

44YY55

**SAFE** FOR USE AROUND  
ELECTRICITY

# STEPLADDERS

## ALUMINUM STEPLADDER

- Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)
- Molded top with handyman's tool slots to keep tools handy
- Slip-resistant rubber feet
- Pinch-resistant spreader braces
- Double-rivet step construction for rail and step reinforcement
- Pail shelf
- Wide standing top (WW-2060-02 only)
- Meets or exceeds requirements of American National Standards Institute

### WW-2010 SERIES STEPLADDER / WW-2060-02 STEP STOOL

Item Number	Ladder Height	Max Reach	Max Standing Ht	Bottom Width	Base Spread	Approx Wt	Approx Cubes
49DJ45	2'	8' 8"	2' 1"	16 1/2"	18"	6 lbs.	1.9'
44YY59	4'	8' 6"	1' 11"	18 7/8"	28"	14 lbs.	3.1'
44YY12	6'	10' 5"	3' 10"	21 7/8"	40"	20 lbs.	5.4'
44YY64	8'	12' 3"	5' 8"	24 7/8"	52"	24 lbs.	8.1'
44YY51	10'	14' 2"	7' 7"	27 7/8"	64"	30 lbs.	11.4'



**ANSI**  
Meets or exceeds requirements of American National Standards Institute

44YY12



## FIBERGLASS STEPLADDER

- Type I duty rated – 250 lbs. load capacity (including weight of user plus materials)
- Molded top with handyman's tool slots to keep tools handy
- Aluminum angel slip-resistant rubber feet protects working surface
- Pinch-resistant spreader braces
- Double-rivet step construction for rail and step reinforcement
- Wide back brace
- Meets or exceeds requirements of American National Standards Institute

### WW-3110 SERIES STEPLADDER

Item Number	Ladder Height	Max Reach	Max Standing Ht	Bottom Width	Base Spread	Approx Wt	Approx Cubes
44YY53*	2'	8' 9"	2' 2"	17"	18"	7 lbs.	1.9'
44YY44	4'	8' 6"	1' 11"	19 1/2"	29"	12 lbs.	3.2'
44YY23	6'	10' 4"	3' 9"	22 1/2"	41"	17 lbs.	5.6'
44YY41	8'	12' 3"	5' 8"	25 1/2"	52"	22 lbs.	8.4'

44YY53 is a folding step stool and is equipped with a large molded top step



**ANSI**  
Meets or exceeds requirements of American National Standards Institute

44YY23



## ALUMINUM STEP STOOL

- Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)
- Wide Step & Platform surface
- Slip-resistant standing surface
- Handrail with locking mechanism
- Casters for transportation
- Non-marring shoes

### WW-2011 SERIES STEP STOOL

Item Number	Ladder Height	Max Reach	Ht to Platform	Bottom Width	Base Spread	Approx Wt	Approx Cubes
44YY25	2'	8' 1"	18"	18"	23"	18 lbs.	1.9'
44YY13	3'	8' 9"	27"	18 7/8"	34"	22 lbs.	2.5'
44YY14	4'	9' 7"	36"	19 5/8"	44"	25 lbs.	3.2'

**DO NOT USE AROUND ELECTRICITY**



## MULTIPURPOSE LADDER

- Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)
- Heavy duty locking pins
- Quick activating snap-lock hinge
- Slip-resistant rubber feet
- 4 ladders in one
- Adjustable; Stairway; Scaffolding; Extension
- Adjustable Height
- Meets or exceeds requirements of American National Standards Institute

### WW-2090 SERIES MULTIPURPOSE LADDER

Item Number	Ladder Height	Bottom Width	Approx Wt	Approx Cubes	Adjustable Stepladder	Stairway	Scaffolding	Extension
44YY66	13'	21 5/8"	24 lbs.	4.2'	3' - 5'	3' - 5'	1' - 2'	7' - 11'
44YY39	17'	25"	29 lbs.	5.7'	4' - 7'	4' - 7'	1' - 3'	9' - 15'
44YY28	22'	28 5/8"	35 lbs.	6.9'	5' - 9'	5' - 9'	1' - 4'	11' - 19'
49DJ47	26'	26"	50 lbs.	11.2'	6' - 11'	6' - 11'	1' - 4'	13' - 23'

**DO NOT USE AROUND ELECTRICITY**



# PLATFORM LADDERS

## ALUMINUM PLATFORM LADDER

- Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)
- Slim, gapless, slip-resistant platform
- Heavy duty gusset bracing for rail and bottom step reinforcement
- Safety top rail guard
- Double-rivet step construction
- Aluminum angle slip-resistant rubber feet and protects working surfaces
- Meets or exceeds requirements of American National Standards Institute

### WW-2040 SERIES PLATFORM LADDER

Item Number	Ladder Height	Max Reach	Ht to Platform	Bottom Width	Base Spread	Approx Wt	Approx Cubes
44YY36	2'	8' 6"	1' 11"	21 7/8"	38"	16 lbs.	7.7'
44YY35	4'	10' 5"	3' 10"	24 7/8"	50"	21 lbs.	12.1'
44YY18	6'	12' 3"	5' 8"	27 7/8"	62"	28 lbs.	17.3'
44YY65	8'	14' 2"	7' 7"	30 7/8"	73"	38 lbs.	23.3'
44YY22	10'	16' 1"	9' 6"	33 7/8"	85"	42 lbs.	30.1'



**ANSI**  
Meets or exceeds requirements  
of American National Standards Institute

44YY35



## FIBERGLASS PLATFORM LADDER

- Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)
- Slim, gapless, slip-resistant platform
- Heavy duty gusset bracing for rail and bottom step reinforcement
- Safety top rail guard
- Double-rivet step construction
- Slip-resistant boots which protects fiberglass and working surfaces
- Meets or exceeds requirements of American National Standards Institute

### WW-3040 SERIES PLATFORM LADDER

Item Number	Ladder Height	Max Reach	Ht to Platform	Bottom Width	Base Spread	Approx Wt	Approx Cubes
44YY26	2'	8' 6"	1' 11"	21 3/8"	38"	17 lbs.	7.7'
44YY11	4'	10' 5"	3' 10"	24 7/8"	50"	24 lbs.	12.1'
44YY31	6'	12' 3"	5' 8"	27 7/8"	62"	28 lbs.	17.3'
44YY10	8'	14' 2"	7' 7"	30 7/8"	73"	41 lbs.	23.3'
44YY27	10'	16' 1"	9' 6"	33 7/8"	85"	55 lbs.	30.1'



**ANSI**  
Meets or exceeds requirements  
of American National Standards Institute

44YY11



# PLATFORM LADDERS

## TYPE IA

■ Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)



■ Professional Top with tool slots



■ Extended 36" front handrail



■ Wide slip-resistant platform



■ Double rivet construction



■ Professional heavy duty boot



**ANSI**  
Meets or exceeds requirements  
of American National Standards Institute

49DJ50

### WW-3043 SERIES PROFESSIONAL PLATFORM LADDER

Item Number	Ladder Height	Max Reach	Ht to Platform	Bottom Width	Base Spread	Approx Wt	Approx Cubes
49DJ48	2'	8' 6"	1' 11"	21 7/8"	38"	19 lbs.	7.7'
49DJ49	3'	9' 5"	2' 10"	23 3/8"	44"	23 lbs.	9.8'
49DJ50	4'	10' 5"	3' 10"	24 7/8"	50"	25 lbs.	12.1'
49DJ51	5'	11' 4"	4' 9"	26 3/8"	56"	28 lbs.	14.6'
49DJ52	6'	12' 3"	5' 8"	27 7/8"	62"	32 lbs.	17.3'
49DJ53	8'	14' 2"	7' 7"	30 7/8"	73"	48 lbs.	23.3'
49DJ54	10'	16' 1"	9' 6"	33 7/8"	85"	64 lbs.	30.1'
49DJ55	12'	18'	11' 5"	36 7/8"	97"	76 lbs.	37.7'

**SAFE** FOR USE AROUND  
ELECTRICITY

## FIBERGLASS PROFESSIONAL PLATFORM LADDER

- Type IAA duty rated – 375 lbs. load capacity (including weight of user plus materials)
- Professional Top with tool slots
- Extended 36" front handrail
- Wide slip-resistant platform
- Double rivet and heavy duty steel reinforcements on every step
- Professional heavy duty boot
- Meets or exceeds requirements of American National Standards Institute

### WW-3443 SERIES PROFESSIONAL PLATFORM LADDER

Item Number	Ladder Height	Max Reach	Ht to Platform	Bottom Width	Base Spread	Approx Wt	Approx Cubes
49DJ56	2'	8' 6"	1' 11"	21 7/8"	38"	19 lbs.	7.7'
49DJ57	3'	9' 5"	2' 10"	23 3/8"	44"	24 lbs.	9.8'
49DJ58	4'	10' 5"	3' 10"	24 7/8"	50"	26 lbs.	12.1'
49DJ59	5'	11' 4"	4' 9"	26 3/8"	56"	29 lbs.	14.6'
49DJ60	6'	12' 3"	5' 8"	27 7/8"	62"	32 lbs.	17.3'
49DJ61	8'	14' 2"	7' 7"	30 7/8"	73"	49 lbs.	23.3'
49DJ62	10'	16' 1"	9' 6"	33 7/8"	85"	64 lbs.	30.1'
49DJ63	12'	18'	11' 5"	36 7/8"	97"	77 lbs.	37.7'




 **SAFE FOR USE AROUND ELECTRICITY**



# FIBERGLASS EXTENSION LADDERS

## TYPE IA

■ Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)




■ Mar-resistant end caps



■ MaxLock™ equipped with QuickLatch® - The strongest, toughest, lightest, rung lock ever.



■ D-shaped rungs



■ Swivel safety shoes



■ Rope and pulley

■ Meets or exceeds requirements of American National Standards Institute

WW-3020 SERIES EXTENSION LADDER						
Item Number	Ladder Height	Max Reach	Max Standing Ht	Max Extended Length	Approx Wt	Approx Cube
44YY67	16'	16' 1"	9' 6"	13'	34 lbs.	6.5'
44YY15	20'	20'	13' 5"	17'	43 lbs.	8.1'
44YY60	24'	23' 10"	17' 3"	21'	50 lbs.	9.6'
44YY49	28'	27' 9"	21' 2"	25'	57 lbs.	11.2'
44YY58*	28'	27' 9"	21' 2"	25'	65 lbs.	11.2'
44YY21	32'	31' 7"	25'	29'	70 lbs.	13.2'
44YY40	40'	37' 5"	30' 10"	35'	93 lbs.	16.4'

\*Includes automatic leveler for uneven surfaces



44YY15

# EXTENSION LADDERS

## EXTENSION LADDER

- Type IAA duty rated – 375 lbs. load capacity (including weight of user plus materials)
- MaxLock™ equipped with QuickLatch® - The strongest, toughest, lightest, rung lock ever.
- Swivel safety shoes double action
- Mar-resistant end caps
- D-shaped rungs
- Rope and pulley
- Meets or exceeds requirements of American National Standards Institute

### WW-3420 SERIES EXTENSION LADDER

Item Number	Ladder Height	Max Reach	Max Standing Ht	Max Extended Length	Approx Wt	Approx Cubes
44YY20	16'	16' 1"	9' 6"	13'	41 lbs.	7.6'
44YY62	20'	20'	13' 5"	17'	50 lbs.	9.4'
44YY57	24'	23' 10"	17' 3"	21'	58 lbs.	11.2'
44YY17	28'	27' 9"	21' 2"	25'	67 lbs.	13.0'



44YY62

## EXTENSION LADDER

- Type IA duty rated – 300 lbs. load capacity (including weight of user plus materials)
- MaxLock™ equipped with QuickLatch® - The strongest, toughest, lightest, rung lock ever.
- Swivel safety shoes double action
- Mar-resistant end caps
- D-shaped rungs
- Rope and pulley (not available on 16' model)
- Meets or exceeds requirements of American National Standards Institute

### WW-2020 SERIES EXTENSION LADDER

Item Number	Ladder Height	Max Reach	Max Standing Ht	Max Extended Length	Approx Wt	Approx Cubes
44YY45	16'	16' 1"	9' 6"	13'	32 lbs.	7.6'
44YY56	20'	20'	13' 5"	17'	38 lbs.	9.4'
44YY46	24'	23' 10"	17' 3"	21'	46 lbs.	11.1'
44YY43	28'	27' 9"	21' 2"	25'	58 lbs.	13.1'

