

## PIG® Burpless® Tall Steel Drum Funnel



DRM1211 For 30 and 55 gal. Steel or Poly Drums w/ 2" NPT, 11.25" x 15" x 13"

Extra height lets you drain containers inside the sealed funnel to cut vapor releases; patented Burpless design delivers fast, no-splash pouring and one-hand latch.

- Drain paint cans and other containers (maximum height 8") while keeping the lid closed to reduce vapor emissions
- Exclusive latching handle design easily opens and closes lid in a simple, single-handed operation
- Burpless design vents during pouring for fast, smooth flow with no dangerous splashback
- Lets you pour without having to vent through  $\frac{3}{4}$ " bung to prevent splashback, a possible closed container reg violation if left open
- Nitrile gasket and latching mechanism completely seal lid to help reduce vapor emissions
- Padlockable to prevent unauthorized access
- Durable, chemical-resistant powder coat helps ensure long service life
- Multiple lid color options let you segregate drums
- Screws securely into a standard 2" bung opening



Item#	Description	Dimensions	Weight
DRM1211-BK	Black	11.25" W x 15" L x 13" H	15.75 lbs.
DRM1211-RD	Red	11.25" W x 15" L x 13" H	15.75 lbs.

### Metric Equivalent:

Item#	Description	Dimensions	Weight
DRM1211-BK	Black	28.6cm W x 38.1cm L x 33cm H	7.1 kg
DRM1211-RD	Red	28.6cm W x 38.1cm L x 33cm H	7.1 kg

### Specifications

<b>Special Feature</b>	Burpless; Vapor Control; Padlockable
<b>Style</b>	Steel Drum Funnel
<b>Use With</b>	30 and 55 gal. Steel or Poly Drums w/ 2" NPT
<b>Dimensions</b>	11.25" W x 15" L x 13" H
<b>Brand</b>	PIG
<b>Drum Bung Opening</b>	2" NPT Bung
<b>Drum Size</b>	30 gal.; 55 gal.
<b>Drainage Space</b>	8.5" H x 9.75" Dia. Draining Area
<b>Drum Type</b>	Steel Drum; Poly Drum
<b>Flame Arrestor Included</b>	No
<b>Lid Type</b>	Latching/Locking Lid
<b>Overfill Preventer Included</b>	No
<b>Sold as</b>	1 each
<b>Weight</b>	15.75 lbs.
<b>New Pig Patent</b>	5,676,185
<b># per Pallet</b>	25
<b>Composition</b>	Funnel - Powder-Coated Steel Lid Gasket - Nitrile Bung Gasket - PTFE
<b>UNSPSC</b>	27112902
<b>Pigalog® Page Number</b>	<a href="#">Page 297</a>

## Metric Equivalent

<b>Dimensions</b>	28.6cm W x 38.1cm L x 33cm H
<b>Weight</b>	7.1 kg

## Technical Information

### Technical Documents

- 29 CFR 1910.106(e)(2)(i)
- 29 CFR 1910.22(a)
- 40 CFR 262.15
- 40 CFR 262.16(b)(2)(iii)
- 40 CFR 262.17(a)(1)(iv)
- 40 CFR 264.1086(c)(1)(ii)

