

PIG® Burpless® Extra-Large Poly Funnel



DRM166 For Steel Drums, Totes and Tanks w/ 2" NPT, 20" x 22" x 10"

Burpless no-splash pouring + huge 7-gallon capacity = our fastest-draining funnel.

- Burpless design vents during pouring for fast, smooth flow with no dangerous splashback
- Lets you pour without venting through 3/4" bung
- Thick-wall, 100% polyethylene construction resists UV rays, rust, corrosion and most chemicals
- Super-wide opening and 7-gallon capacity make this our fastest draining funnel, ideal for IBC fills
- Ridged interior creates a level draining surface for containers and promotes faster draining
- Built-in debris strainer captures large particles



Item#	Description	Dimensions	Weight
DRM166-RD	Red,	20" W x 22" L x 10" H	18.977 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
DRM166-RD	Red,	50.8cm W x 55.9cm L x 25.4cm H	8.6 kg

Specifications

Drum Lid Closure	Tight-Head
Special Feature	Burpless; Padlockable
Use With	Steel Drums, Totes and Tanks w/ 2" NPT
Dimensions	20" W x 22" L x 10" H
Drum Bung Opening	2" NPT
Drainage Space	23" L x 15.5" W x 4" H Draining Area
Drum Type	Steel
Flame Arrestor Included	No
Lid	With Hinged Lid
Overfill Preventer Included	No
Sold as	1 each

Weight	18.977 lbs.
# per Pallet	5
Composition	Funnel- Polyethylene Threaded Insert - Brass
UNSPSC	27112902
Pigalog® Page Number	<u>Page 313</u>

Metric Equivalent

Dimensions	50.8cm W x 55.9cm L x 25.4cm H
Weight	8.6 kg

Technical Information

Technical Documents

[LDPE Products](#)

Disclaimers

[Flammables Warning](#)

Not for use with flammables (f.p.<141°F/60.5°C).



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com