

LED Replacement Lamps

LED PAR20 Directional Lamp



Project Name _____

Date _____ Type _____

Notes _____

The bright white radiance of the Current's LED PAR20 lamps isn't just something you see, it's something you feel. For hard-to-reach downlight applications, Current's dimmable 7-watt LED PAR20 lamp is the ideal solution.

PERFORMANCE HIGHLIGHTS:

PAR20 Lamps	
Light Output Range:	430-520 Lumens
CRI:	Up to 90 CRI
CCT:	2700K & 3000K
Input Voltage:	120
Efficiency:	Up to 72 LPW
Wattage:	7W
Life:	25,000 hours L70
Temperature Rating:	-20°C to 45°C
Rating:	Damp
Dimmable:	Dims from 100% to 10%

LIMITED WARRANTY

3 Years

FEATURES:

- Halogen-like color
- Available in different beam patterns
- These lamps are energy efficient, contain no lead or mercury

BENEFITS:

Energy + Cost Savings

- For example, using only 7 watts of energy, save over \$236 in energy costs over the life of the lamp versus a standard 35-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent or halogen light sources

LEARN MORE:

To learn more about saving money and energy, go to www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LED Replacement Lamps

LED PAR20 Directional Lamp

Spec Table

Project Name _____

Date _____ Type _____

Notes _____

Base Type	Order Type	Watts	Order Code	Description	Case Volts	MOL Qty**	Lumens (In)	Initial CBCP	Initial Color		Wattage Replacement	*Rated Life		ENERGY STAR® Status	# Location Rating	Additional Information	
									Temp	CRI		L70 (Hrs)	Dimmable				
COMPACT PAR20																	
PAR 20	E26	7	93107782	LED7DP203W927/35	120	6	3.5	430	1000	2700	90	50	25,000	Yes	–	Damp	Flood, 35° beam
	E26	7	93107783	LED7DP203B927/35	120	6	3.5	430	1000	2700	90	50	25,000	Yes	–	Damp	Flood, 35° beam, Black Casing
	E26	7	93327	LED7DP203B830/20	120	6	3.5	520	3600	3000	80	50	25,000	Yes	★	Damp	Narrow Flood, 20° beam, Black Casing
	E26	7	93347	LED7DP203W830/20	120	6	3.5	520	3600	3000	80	50	25,000	Yes	★	Damp	Narrow Flood, 20° beam
	E26	7	93348	LED7DP203W830/35	120	6	3.5	520	1200	3000	80	50	25,000	Yes	★	Damp	Flood, 35° beam
	E26	7	93349	LED7DP203B827/20	120	6	3.5	500	3600	2700	80	50	25,000	Yes	★	Damp	Narrow Flood, 20° beam, Black Casing
	E26	7	93354	LED7DP203B827/35	120	6	3.5	500	1150	2700	80	50	25,000	Yes	★	Damp	Flood, 35° beam, Black Casing
	E26	7	93360	LED7DP203W827/20	120	6	3.5	500	3600	2700	80	50	25,000	Yes	★	Damp	Narrow Flood, 20° beam
	E26	7	93362	LED7DP203W827/35	120	6	3.5	500	1150	2700	80	50	25,000	Yes	★	Damp	Flood, 35° beam

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.