


ALTERNATING TREAD STAIR - ATS-10-56

APPROX WEIGHT: 253.10 lbs.
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE



| | |
|---|--|
| FOR INTERNAL USE ONLY PROJECT SIGN OFF | |
| SALES | |
| ENG. | |
| FAB. | |
| POWER | |

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

DIMENSION TOLERANCE ± 1/4"

- STANDARD FEATURES**
- MODEL NUMBER: ATS-10-56
 - CLIMB ANGLE: 56°
 - NUMBER OF STEPS: 16 (INCLUDING TOP STEP)
 - TOP STEP HEIGHT: 120"
 - STEP HEIGHT SPACING: 7 1/2"
 - HANDRAIL HEIGHT: 18 5/8"
 - OVERALL HEIGHT: 162 3/8"
 - OVERALL LENGTH: 89 3/4"
 - OVERALL WIDTH: 23 1/2"
 - CHAIN GATES AT TOP STEP
 - RUBBER BUMPER STRIP
 - MAX CAPACITY IS 350 LBS
 - TOUGH BAKED IN POWDER COATED YELLOW FINISH

SPECIAL FEATURES
NONE

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

ANY MODIFIED UNITS ARE NON-RETURNABLE

[] As drawn [] As marked

Signed: _____ Date: _____

Printed Name: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

| | | |
|----------------------|-------------|------------|
| DISTRIBUTOR'S NAME: | | P.O.# |
| VESTIL MANUFACTURING | | X |
| DRAWN BY: B.WOOD | | W.O.# |
| DATE: 4/22/2009 | | X |
| REFERENCE: X | SCALE: 1:30 | SALES: X |
| QUOTED LEAD TIME: X | QUOTE # X | FILE NAME: |
| | | 44-007-240 |