

# ASPEN™-6 / ASPEN™-10

Backpack Vacuums



# Finally, affordable backpack vacuums that are comfortable

## Aspen™-6 / Aspen™-10

### Comfort leads to productivity

An ergonomic Deuter® branded hiking harness designed to decrease muscle fatigue and maximize operator comfort and mobility.

### Safe, field-proven performance

Enhanced safety features, such as added strain relief, 67 dBA noise level and 4-stage filtration with HEPA means you can clean safer and protect your investment.

### Options to suit your cleaning needs

With three tool kits available, you can choose the set that's right for your application. The premium Sidewinder® kit provides up to 50% more productive cleaning than traditional push-pull wands.



## Three no-nonsense features

### 1. Kettle Plug



### 2. Sidewinder Tool



### 3. Affixed on/off switch





## Deuter® Harness

Designed and manufactured by Deuter, the world leader in hiking backpacks.

Adjustable to operator height (operator comfort)

Stabilizer Straps for exact positioning (ergonomics and safety)

Anatomically cut hip belt (ergonomics and operator comfort)

Anatomically shaped shoulder straps (operator comfort)

Breathable mesh provides 3D airflow, reducing operator exertion (productivity and operator comfort)

View our demonstration videos at [nobles.com/asp6\\_10](https://nobles.com/asp6_10)

## Tool kits

### Base Kit

Two-piece locking aluminum wand with 14 in / 356 mm tools



### Standard Telescoping Kit

Chrome telescoping wand with 14 in / 356 mm tools



### Premium Sidewinder® Kit

Two-piece anodized aluminum wand with 18 in / 457 mm Sidewinder tools.



UP TO 50% MORE PRODUCTIVITY



**REDUCE COST TO CLEAN**

- Maximize productivity with new features such as sidewinder tool and ergonomic harness.
- Improve efficiency, mobility and productivity through use of ergonomic backpack vacuum.
- Three new tool kit options to suit a variety of cleaning needs.



**HEALTH AND SAFETY**

- Increased comfort and mobility for operator due to new ergonomic harness.
- Minimize safety risks and damage with new cord strain relief and affixed on/off switch accessed on the belt.



**IMAGE**

- Improve facility image through 4-stage filtration with HEPA.



**SUSTAINABILITY**

- LEED qualifying CRI certified vacuum maintains air quality through 4-stage filtration with HEPA.

**The Nobles Aspen-6/Aspen-10 is the smart, reliable choice for your no-nonsense cleaning needs.**

**Nobles**

701 North Lilac Drive  
Minneapolis, MN 55422

USA/Canada: +1.800.553.8033

Quebec: +1.800.361.9050

www.nobles.com

nobles@tennantco.com

| Aspen™-6/Aspen™-10 Specifications |  |
|-----------------------------------|--|
| Airflow at 2 in / 50 mm orifice   | 111 cfm / 189 m3/h                                     |
| Vacuum motor hp                   | 11.6 hp / 1.2 kW each                                  |
| Vacuum motor type                 | Single stage, thermal protected                        |
| Vacuum motor watts/amps           | 1200 watts / 10 A                                      |
| Water lift at sealed orifice      | 119 in / 3023 mm                                       |
| 4-stage filtration system         | Cloth bag, filter bag, HEPA filter, and exhaust filter |
| Triple filtration description     | High efficiency (99.97%) at 0.3 micron                 |
| Vacuum hose length                | 12 ft / 3.7 m (4:1 stretch ratio)                      |
| Vacuum bag capacity               |  |
| Aspen-6                           | Fill design, 5.2 qt / 4.9 L                            |
| Aspen-10                          | Fill design, 9.2 qt / 8.7 L                            |
| Power cord length                 | 50 ft / 15 m, safety-yellow power cord                 |
| Product weight                    |  |
| Aspen-6                           | 13 lb / 5.9 kg   |
| Aspen-10                          | 13.5 lb / 6.1 kg                                       |
| Sound level (operator's ear)      | 67 dBA   |
| Approvals                         |  |
| UL (US/CAD)                       | Yes  |
| Max CRI rating*                   | Gold certified with high-performance tool              |
| Warranty                          | See your local representative for warranty information |

\* See CRI Website for further information  
Specifications subject to change without notice.

