IEC Pin and Sleeve

100A, 125/250V, 3 Pole, 4 Wire

Corrosion Resistant Watertight Receptacle

Features

- UL Type 4X, 12 and IP69k environmental ratings
- Super tough insulated non-metallic housing
- Self-closing gasketed cover
- Sequential contact engagement to prevent a momentary over-voltage
- Market leading UL witnessed HP ratings

Ordering Information

Description Watertight IEC Pin and Sleeve Receptacle

UPC 783585410050 **Catalog Number** M4100Ř12

Listings

UL Listed. File E146032

UL Classified to IEC 60309-1 IEC 60309-2

Specifications

Housing Closure Covers

Sealing Gasket Retainer

Gaskets Terminal Screws **PBT** PBT

Solid Neoprene **High-Impact Thermoset**

Santoprene Stainless Steel

Performance

Electrical

Current Interrupting

Certified for current interrupting at full rated

current Withstand 3000V AC

Dielectric Voltage

600V RMS

Max. Working Voltage

Mechanical

Impact Resistance

Per CSA C22.2 No. 182.1 / UL1682

Product Identification

Identification and ratings are a permanent part of

the device housing

Terminals identified in accordance with North **Terminal Identification**

American and IEC conventions

Environmental

Moisture Resistance

Flammability V-0

Type 3R,3RX,4X AND IP68,IP69K Ingress Protection

IEC 60309-1

Operating Temperatures Maximum Continuous 75°C; Minimum - 40°C

w/o impact

Complementary Products

Cover Assemblies


Online Resources

Customer Sales Drawing eCatalog

Installation Instructions

HUBBELL







Wiring Device-Kellems