



Available Colors: Navy, Charcoal, Brown, Red/Black, Hunter Green and Burgundy



Uptown™ is a high-low looped pile entrance mat that dries shoes and retains moisture and debris, while offering an upscale, elegant look. 40 ounces of tufted Decalon® yarn per square yard offer the ultimate in moisture absorption and crush resistance for use in the heaviest traffic areas. Uptown™ has a heavyweight vinyl backing available in corresponding colors to ensure minimum mat movement and enhance the aesthetic appeal of the mat. Uptown's colors correspond with the Boulevard™ mat to be used together as an upscale scrape & dry entrance matting system.


Test	Test Description	*Results
ASTM D-6540-00	Accelerated Soiling of Pile Yarn	Rating After Vacuum 4.0 Rating After Extraction 5.0
ASTM D412	Breaking Load and Elongation	346.8 lbs/in ²
ASTM D5252-98a	Accelerated Wear - 4,000 cycles (Hexapod Tumble Drum Tester)	Appearance: 3.0 Color: 3.5
ASTM D3936-0	Delamination	Exceeds Backing Strength
CPSC FF 1-70 (ASTM D-2859)	Surface Flammability of Carpets and Rugs Ignition Characteristics - Finished Textile Floor Covering Material	Pass
-	Water Retention	Weight Gain = 291.08% (0.992 gals./yd ²)
ASTM D2240-02	Durometer Hardness	70
ASTM D1335-98	Tuft Bind of Pile Yarn	10.4 = Superior

*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

07/2014

Appearance Rating Key	
5	No change
4	Slight change
3	Noticeable change
2	Considerable change
1	Severe change

- 40 oz. face weight
- Thickness: 3/8"
- Heavyweight vinyl non-slip backing
- Stock Sizes: 2' x 3', 3' x 4', 3' x 5', 3' x 6', 3' x 10', 4' x 6', 4' x 8'
- Roll Sizes: 3' x 60', 4' x 60', 6' x 60' Custom Sizes: In 3', 4', and 6' widths (up to 60')
- Recommended and approved product as part of the GreenTRAX™ program for "Green Cleaning" environments



Custom Sizes