



SPECIFICATIONS

INSTRUMENT WARRANTY:

Three year warranty which does not include battery, sensors and filters.*
CO and H₂S sensors are warranted for 3 years from the initial purchase date.
All other sensors are warranted for 2 years from the initial purchase date.

DISPLAY:

Segment liquid crystal display (LCD)

KEYPAD:

Two buttons

CASE MATERIALS:

Case top: Polycarbonate with a protective rubber overmold
Case bottom: Conductive polycarbonate

ALARMS:

Three strobe-emitting visual alarm LEDs (two red; one blue);
100 decibel (dB) audible alarm at a distance of 10 cm (3.94"); Vibration alarm

DIMENSIONS:

99 x 51 x 35 mm (3.9" x 2.0" x 1.4")

WEIGHT:

126.0 g (4.4 oz.)

TEMPERATURE RANGE:

-40°C to +50°C (-40°F to +122°F)†

HUMIDITY RANGE:

15%-95% Non-condensing (continuous)

SENSORS:

CO, CO/H₂, H₂S, NO₂, SO₂ - Electrochemical sensor technology

SENSOR MEASURING RANGES:

Carbon Monoxide (CO): 0 to 1,000 ppm in 1 ppm increments
Carbon Monoxide (CO/H₂ low): 0 to 1,000 ppm in 1 ppm increments
Hydrogen Sulfide (H₂S): 0.0 to 200.0 ppm in 0.1 ppm increments
Nitrogen Dioxide (NO₂): 0.0 to 150.0 ppm in 0.1 ppm increments
Sulfur Dioxide (SO₂): 0.0 to 150.0 ppm in 0.1 ppm increments

BATTERY:

3.6 V Primary lithium-thionyl chloride (Li-SOCI₂); 1.5AH, 2/3AA; replaceable;
non rechargeable; always on; 3 year run time depending on operating conditions

DATALOGGING:

3 months at 10-second intervals

EVENT LOGGING:

60 alarm events

CERTIFICATIONS

INGRESS PROTECTION:

IP66; IP67

-40°C to +50°C (-40°F to +122°F)

ATEX Ex ia I Ma
Ex ia IIC T4 Ga
Equipment Group and Category: I M1 and II 1G
CSA Ex ia IIC; Class I, Groups A B C D; T4
IECEX Ex ia I Ma
Ex ia IIC T4 Ga
UL (C-US) Class I, Groups A, B, C, and D; Class II, Groups E, F, and G; T4; Exia
Class I, Zone 0, AEx ia IIC T4
INMETRO Ex ia IIC T4 Ga; Ex ia I Ma

-20°C to +50°C (-4°F to +122°F)

China Ex Ex ia IIC T4 Ga
KOSHA Ex ia IIC T4

These specifications are based on performance averages and may vary by instrument.

* The Tango is warranted to be free from defects in material and workmanship under normal and proper use and service for 3 years from the initial purchase date.

† Operating temperatures above 50°C (122°F) may cause reduced instrument accuracy. Operating temperatures below -20°C (-4°F) may cause reduced instrument accuracy and affect display and alarm performance.



ORDERING INFORMATION

PART NO.	DESCRIPTION
INSTRUMENT CONFIGURATIONS	
TX1-1	Tango TX1, CO
TX1-2	Tango TX1, H ₂ S
TX1-4	Tango TX1, NO ₂
TX1-5	Tango TX1, SO ₂
TX1-G	Tango TX1, CO/H ₂ low
ACCESSORIES	
18109330-ABC -ABC	DSX™ Docking Station for Tango™ TX1 A – DSX Mode: 0 = DSX Standalone, 1 = DSXi Cloud-connected, 2 = DSX-L Local Server B – Number of Gas Inlet Ports: 3 = 3 Ports, 6 = 6 Ports C – Power Cord Type: 0 = None, 1 = North America, 2 = Europe, 3 = Australia, 4 = UK
17154367	Replacement battery
18109171	Soft nylon case, Black
18109239	Soft nylon case, Orange
18109218	Dust barrier kit, 5 pack
18109230	Water barrier kit, 5 pack
18109238	CalCup and tubing kit
17120908	Belt clip
17154915-0	AlarmAmp™, Black
17154915-1	AlarmAmp™, Safety Orange
17154916	Black nameplate
17154917	Green nameplate
17154918	Yellow nameplate
17154919	Blue nameplate
17154920	White nameplate

INDUSTRIAL SCIENTIFIC

www.indsci.com

AMERICAS

Phone: +1-412-788-4353
1-800-DETECTS (338-3287) North America
Fax: +1-412-788-8353
info@indsci.com

ASIA PACIFIC

Phone: +65-6561-7377
Fax: +65-6561-7787
info@ap.indsci.com

EMEA

Phone: +33 (0)1 57 32 92 61
Fax: +33 (0)1 57 32 92 67
info@eu.indsci.com

