Flexible-tube luminaire SLF 500/750

113261000-00641183



fitted with

work equipment connected load power consumption luminous flux luminous efficacy light distribution light color color rendering index (CRI) glare-free system of protection class of protection technology usage luminaire body lamp cover tubular sections weight (net) mains lead

fastening special features

LED

electronic plug-in transformer 100-240 V; 50/60 Hz approx. 6 W approx. 460 lm approx. 77 lm/W direct, wide-angled beam neutral white, approx. 5000 K > 70 screen IP 67 II with plug-in power supply; III without plug-in power supply switchable pressure switch aluminium, painted, black glass screen flexible metal tube, black approx. 1.7 kg (3.7 lbs) approx. 3 m (9.8 ft); mains plug US and foreign plugs included

Waldmann W

ENGINEER OF LIGHT.

screw-down flange Flood with 30° angle of radiation

CE





BS 1363 A

CEE 7/XVI

NEMA 1-15P

illuminance

2969 lx 5298 lx 1085 lx

distance: 50 cm

Em: Emax Emin:





luminous intensity





Errors and technical changes excepted. Images can vary from original. Photometric and electrical data may vary due to component tolerances.