

# TORK<sup>®</sup> nsi INDUSTRIES

## SPECIFICATION SHEET

Project Info:	Type:
Job Ref:	Catalog Number:
Approvals:	Date:

### 8009A

#### 24 Hour Duty Cycle Time Switch

#### OVERVIEW

Daily On/Off Operations per Day Duty Cycle Timer

#### APPLICATIONS & FEATURES

- Duty Cycling
- Ventilating Fans
- Pumping
- Irrigation
- Process control
- Laboratory experiments
- For one or multiple daily ON/OFF operations
- Scheduling: Minimum On setting is 15 minutes with minimum off setting at 15 minutes. Dial has 96 captive tabs.
- Duty Cycle: Adjustable from 1/2, 1, 2, 3, 4, 6, 12, and 24 hours.
- Standards: Listed UL917


#### SPECIFICATIONS

- Switch: SPDT
- Contact Ratings:
  - 20Amp 125/250/480VAC
  - 3/4 HP 125VAC 1 1/2 HP 250VAC
- Timing Motor: 120/208-277VAC 60Hz
- Power Consumption 3.5 Watts Max



8009A  
24 Hour Duty Cycle Time Switch

#### DIMENSIONS



#### LIMITED WARRANTY

- 1 -year manufacturer's warranty