HUBBELLPRO Ground Fault Receptacle AUTOGUARD® Self Test GFCI 15A, Tamper-Resistant

HUBBELL

Features

- · Autoguard self-test technology with auto-monitor, power denial
- · Patented tamper-resistant mechanism designed specifically for residential applications provides ease of insertion
- Flush, smooth profile and satin finish complement any décor



Ordering Information

Description	Color	UPC Number	Catalog Number
15A, 125V, Style Line®, AUTOGUARD® self test GFCI receptacle, tamper-resistant, flush face, back and side wired	White	883778450662	GFT15W

10	šti	ın	α	c

UL Listed - Canadian and U.S.	CSA Certified
Meets ADA Standard	NEMA WD-6 Complaint
Meets are NEC requirements	·

Specifications

opcomoduono	
Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Galvanized Steel
Mounting Screw	Zinc Plated Steel

Performance


15A, 20A Feed Thru
Certified for current interrupting at full rated current
Withstands 1,500V minimum
60 Hz
10,000A
4 to 6 mA
0.25 second nominal
120 AC +10% - 15% (102V to 132V)

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14 - 10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 948 and CSA

	Environmental		
Flammability		V2 per UL 94	
	Operating Temperature	-35 C to 66 C or -30 F to 150 F	





Accessories

Wall plate not included

Links

Customer Drawings Instruction Installations Media

