



Main

Product or Component Type	Cover
Protection Type	Fingersafe

Complementary

Product destination	Transformer
Voltage Codes	D1 250...5000 VA D2 250...5000 VA D3 250...5000 VA D4 250...5000 VA D5 250...5000 VA D13 250...5000 VA D14 250...5000 VA D33 250...5000 VA D37 250...5000 VA D15 250...5000 VA D20 250...5000 VA D23 250...5000 VA D31 250...5000 VA D32 250...5000 VA
Quantity per Set	Set of 2
Height	1.669 in (42.39 mm)
Width	2.374 in (60.30 mm)
Depth	0.992 in (25.20 mm)

Ordering and shipping details

Category	16204 - 9070 T FUSE BLOCKS & ACCES
Discount Schedule	CP8
GTIN	785901904755
Nbr. of units in pkg.	1
Package weight(Lbs)	1.28 oz (36.287 g)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.20 in (3.048 cm)
Package 1 width	2.80 in (7.112 cm)
Package 1 Length	4.40 in (11.176 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	16.80 oz (476.272 g)
Package 2 Height	5.60 in (14.224 cm)

Package 2 width	6.50 in (16.51 cm)
Package 2 Length	7.20 in (18.288 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	240
Package 3 Weight	27.63 lb(US) (12.533 kg)
Package 3 Height	11.70 in (29.718 cm)
Package 3 width	21.20 in (53.848 cm)
Package 3 Length	29.50 in (74.93 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------