



**MCR  
SAFETY**

# 9687 Flex Tuff Cut Protection Specification Sheet

**PRODUCT DESCRIPTION:**

Cut the Bull, not your hands! Kevlar® is the world's most cut resistant fiber and the latex rubber coating adds the grip and abrasion resistance you need to cut into the job, not your hands. Made of 100% DuPont™ Kevlar® fibers, the 9687 shell offers breathability, comfort, manual dexterity and is launderable. It has a blue latex palm and finger coating.

**FEATURES:**

- High comfort level
- 10 Gauge DuPont™ Kevlar® Fibers
- Blue Latex Palm and Fingertips
- Shell is 100% DuPont™ Kevlar® and palm is natural latex rubber, neither of which will conduct electricity

**APPLICATIONS:**

Automotive Assembly, Farming, Landscaping, Carpentry, Construction, Janitorial, Material Handling, Metal fabrication, Recycling



**TECHNICAL DATA FOR: 9687**

<b>Series</b>	Flex Tuff	<b>EN 388 : CE Score - Abrasion</b>	3
<b>Material Group</b>	Strings	<b>EN 388 : CE Score - Cut</b>	4
<b>Product Type</b>	Cut Protection	<b>EN 388 : CE Score - Tear</b>	4
<b>Glove Size</b>	Large	<b>EN 388 : CE Score - Puncture</b>	3
<b>Gauge</b>	10 Gauge	<b>ANSI Cut</b>	ANSI Cut A3
<b>Material</b>	Kevlar	<b>ANSI Puncture</b>	ANSI Puncture 5

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved



**MCR**  
SAFETY

# 9687

## Flex Tuff

### Cut Protection

### Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9687L	Large	9.84	5.60	2.95	37.452 lb.	3.121
9687M	Medium	9.25	5.52	2.56	33.348 lb.	2.779
9687S	Small	8.66	5.16	2.56	29.676 lb.	2.473
9687XL	X - Large	10.43	5.88	3.15	41.364 lb.	3.447
9687XXL	XX - Large	11.62	5.84	3.35	42.504 lb.	3.542

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved