


# PD8

## Power Distribution Module

### Description

Altronix PD8 power distribution module is designed to convert a single AC or DC input into eight (8) individually fuse protected outputs.



PD8

### Specifications

#### Input

Voltage Range 28VAC or 28VDC max., up to 12A.

#### Outputs

Eight (8) fuse protected outputs.  
 2.5A per output max.  
 Total output current should not exceed max current rating of power supply employed.  
 Fuses are rated @ 3.5A/250V.

#### Indicators (LED)

DC Output Power LED.

#### Physical and Environmental

##### Dimensions (L x W x H)

5.25" x 3.25" x 1" (133.4mm x 82.6mm x 25.4mm).

Product Weight 0.25 lbs. (0.11 kg).

Shipping Weight 0.3 lbs. (0.14 kg).

##### Temperature

Operating 0°C to 49°C (32°F to 120°F).

Storage -20°C to 70°C (-4°F to 158°F).

Relative Humidity 85% +/-5%.

### Board Dimensions (L x W x H) and Drawing

5.25" x 3.25" x 1" (133.4mm x 82.6mm x 25.4mm)

