

DEWALT

20V MAX*
LITHIUM ION **XR**
BRUSHLESS

**PERFORM
PROTECT™**

3.5 JOULES
AND 1,000 RPM**

For fast and efficient drilling,
even hard concrete

SHOCKS

SHOCKS ACTIVE VIBRATION
CONTROL SYSTEM®
reduces vibration felt by the
user at the handles

**SDS+ TOOL
HOLDER**

Optimized drilling
range between
1/2" & 7/8"

E-CLUTCH

The DEWALT E-Clutch® system
senses the motion of the tool
and reduces the motor torque
to a manageable level
if necessary

**CORDED
MECHANISM**

For long
service life and
high performance

DUST COLLECTION

Attachment points for a
Table 1 compliant solution

INCLUDES



DCB206 (6.0 AH)



DCB115

DEWALT's Perform & Protect™ line of tools is designed to provide a high level of one or more of the following: control, dust containment or low vibration, without sacrificing performance.

*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

**According to EPTA-Procedure 05/2009

DEWALT
ENGINEERED BY POWERS

FASTENERS 5/32"-1/2" FOR OPTIMAL USE



POWER BOLT+® ANCHOR



POWER-STUD+™



ADHESIVE ANCHORING



SCREW-BOLT+® ANCHOR



**20V MAX* XR® BRUSHLESS 1-1/8" L-SHAPE
SDS+ ROTARY HAMMER KIT**

DCH293R2

SPECIFICATIONS

No Load Speed	0-1000 rpm
BPM	0-4480 bpm
Optimal Drilling Range	5/8"-7/8" (16-22 mm)
Impact Energy	3.5 Joules**
Chipping	Yes
Vibration Measurement	7.5 m/s ²
Tool Weight (Tool only)	8.21 lbs (3.72 kg)

TOOL WARRANTY



BATTERY WARRANTY



YOUR FIRST LINE OF DEFENSE.™

REDUCES SILICA DUST EXPOSURE WHILE DELIVERING THE PERFORMANCE YOU EXPECT.

RELATED PRODUCTS



DCH293B
20V MAX* XR® BRUSHLESS 1-1/8" L-SHAPE SDS PLUS ROTARY HAMMER (BARE)



DCH293X2
20V MAX* XR® BRUSHLESS 1-1/8" L-SHAPE SDS PLUS ROTARY HAMMER



DWH304DH
DUST EXTRACTOR
OSHA COMPLIANT VERSION AVAILABLE SEPT. 2017



DW5474
SDS+ FULL HEAD CARBIDE MASONRY DRILL BITS

www.DEWALT.com 1-800-4-DEWALT

Copyright ©2017 DEWALT. The following are examples of trademarks for one or more DEWALT power tools, accessories, anchors, and concrete adhesives: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.